



# Softone Globe

## Softone Globe 20W WW E27 G120 1CH/4

Decorative covered energy-saving lamps for consumer applications

### Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

### Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime	10,000 h
Switching Cycle	30,000
Rated Lifetime (Hours)	10,000 h
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Colour Code	827 [CCT of 2700K]
Luminous Flux	1,140 lm
Colour designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Correlated Colour Temperature	2700 K
Luminous efficacy (rated) (nom.)	57 lm/W
Colour rendering index (CRI)	82
LLMF at end of nominal lifetime (nom.)	65 %

Operating and Electrical	
Line Frequency	50 or 60 Hz
Input frequency	50 or 60 Hz
Power Consumption	20.0 W
Lamp current (nom.)	141 mA
Starting time (nom.)	0.3 s
Warm-up time to 60% light	10-100 s s
Power Factor (Fraction)	0.6
Voltage (nom.)	220-240 V

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb shape	G120 [G 120 mm]


Approval and Application	
Mercury (Hg) content (max.)	2.0 mg
Mercury (Hg) content (nom.)	1.5 mg

Softone Globe

Energy consumption kWh/1,000 hours	20 kWh
Product Data	
Order product name	Softone Globe 20W WW E27 G120 1CH/4
Full product name	Softone Globe 20W WW E27 G120 1CH/4
Full EOC	871150083015945
Order code	83015945

Material no. (12 NC)	929689171103
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500830159
Numerator – packs per outer box	4
EAN/UPC - Case	8711500830975

Dimensional drawing



Product	C (max)	F (max)
Softone Globe 20W WW E27 G120 1CH/4	182 mm	48.2 mm

