



# Economy Twister

## EconomyTwister 12W WW E14 220-240V 1PF/6

Compact Entry Spiral shape energy saving lamp, starts bright light rapidly and fits everywhere. It saves your money due to its low energy consumption. With a comprehensive range of wattages, it enables easy replacement of most incandescent lamp all the way

### Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

### Product data

General Information	
Cap-Base	E14
Nominal lifetime	6,000 hour(s)
Switching Cycle	6,000
Rated Lifetime (Hours)	6,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	741 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	61 lm/W
Color rendering index (CRI)	81

LLMF At End Of Nominal Lifetime (Nom) 70 %	
Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	12.0 W
Lamp Current (Nom)	90 mA
Starting Time (Nom)	0.3 s
Warm-up time to 60% light	5-40 s s
Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No

# Economy Twister

## Mechanical and Housing

Bulb Shape	Spiral
------------	--------

## Approval and Application


Mercury (Hg) Content (Max)	2.0 mg
Energy Consumption kWh/1000 h	12 kWh

## Product Data

Order product name	EconomyTwister 12W WW E14 220-240V 1PF/6
Full product name	EconomyTwister 12W WW E14 220-240V 1PF/6

Full product code	871829121705300
Order code	21705300
Material Nr. (12NC)	929689238501
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291217053
Numerator - Packs per outer box	6
EAN/UPC - Case	8718291217060

## Dimensional drawing



Product	D (max)	C (max)	F (max)
EconomyTwister 12W WW E14 220-240V 1PF/6	47.5 mm	104 mm	40.5 mm

