



GENIE

GENIE 11W WW E27 220-240V 1PF/6

Functional non-covered Energy saving lamp, with money saving high quality light and compact design. This lamp is small enough to fit neatly wherever you need extra bright light at home, enables easy replacement of most incandescent lamp all the way.

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Product data


General Information	
Cap-Base	E27 [E27]
Nominal lifetime	10,000 hour(s)
Switching Cycle	10,000
Rated Lifetime (Hours)	10,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	600 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	55 lm/W
Color rendering index (CRI)	80

LLMF At End Of Nominal Lifetime (Nom)	65 %
Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	11 W
Lamp Current (Nom)	80 mA
Starting Time (Nom)	0.3 s
Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Shape	Stick
Approval and Application	
Mercury (Hg) Content (Max)	2 mg
Mercury (Hg) Content (Nom)	1.5 mg
Energy Consumption kWh/1000 h	11 kWh
Product Data	
Order product name	GENIE 11W WW E27 220-240V 1PF/6

Full product name	GENIE 11W WW E27 220-240V 1PF/6
Full product code	871150080119710
Order code	80119710
Material Nr. (12NC)	929689243301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500801197
Numerator - Packs per outer box	6
EAN/UPC - Case	8711500801692

Dimensional drawing



Product	D (max)	C (max)	F (max)
GENIE 11W WW E27 220-240V 1PF/6	35.0 mm	115 mm	44.5 mm

