



GENIE

Genie 23W WW E27 220-240V 1PF/6

Functional non-covered Energy saving lamp, with money saving high quality light and compact design. This lamp is small enough to fit neatly wherever you need extra bright light at home, enables easy replacement of most incandescent lamp all the way.

Warnings and safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.



Produktdata

Generell informasjon		Nominell vedlikeholdsfaktor for lyskildelumen ved 65 % utgangen av nominell levetid (nom.)	
Sokkelbase	E27 [E27]		
Nominell levetid	10 000 time(r)		
Brytersyklus	10 000		
Anslått levetid (timer)	10 000 time(r)		
Lighting Technology	Compact Fluorescent Integrated		
Teknisk belysning		Drift og elektronikk	
Fargekode	827 [CCT of 2700K]	Line Frequency	50 or 60 Hz
Lysytelse	1 450 lm	Inngangsfrekvens	50 eller 60 Hz
Fargebetegnelse	Varmhvit (WW)	Effektforbruk	23 W
Kromatisk koordinat X (nom)	463	lyskildestrøm (nom.)	165 mA
Kromatisk koordinat Y (nom)	420	Starttid (nom.)	0,3 s
Korreleret fargetemperatur (nom)	2700 K	Tiden det tar før lyset er på 60 %	5-40 s s
Lysutbytte (vurdert) (Nom)	62 lm/W	Effektfaktor (brøk)	0.6
Fargegjengivelsesindeks (CRI)	80	Spennning (nom.)	220-240 V
		Kontroller og dimming	
		Kan dimmes	Nei

Mekanikk og innfatning	
Lyspæreform	Stav
Godkjenning og bruksområde	
Kvikksølv (Hg)-innhold (maks.)	2 mg
Lavt kvikksølv (Hg)-innhold (nom.)	1,5 mg
Energiforbruk kWh/1000 t	23 kWh
Produktdata	
Produktnavn for bestilling	Genie 23W WW E27 220-240V 1PF/6
Fullstendig produktnavn	Genie 23W WW E27 220-240V 1PF/6

Full EOC	872790089713501
Lokal kodebeskrivelse	3811200
Bestillingskode	89713501
Materialenr. (12NC)	929689243901
Lokal bestillingskode	3811200
SAP-teller – antall per pakke	1
EAN/UPC – produkt/boks	8727900897135
SAP-teller – pakker per utvendige	6
EAN/UPC – boks	8718291657798

Målskisse



Product

Genie 23W WW E27 220-240V 1PF/6

Product	D (max)	C (max)	F (max)
Genie 23W WW E27 220-240V 1PF/6	36 mm	157,0 mm	48,5 mm

