



Tornado T3

Tornado T3 32W WW E27 220-240V 1PF/6

Tornado has outstanding brightness which makes your colors appear more Vivid. It allows easy replacement of high wattage of incandescent lamps.

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	8,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	8,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	2,255 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	463
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	80
Operating and Electrical	
Line Frequency	50 or 60 Hz


Input Frequency	50 or 60 Hz
Power Consumption	32.0 W
Lamp Current (Nom)	140 mA
Starting Time (Nom)	0.3 s
Warm-up time to 60% light	5-40 s s
Power Factor (Fraction)	0.95
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	Spiral
Approval and Application	
Mercury (Hg) Content (Max)	2.5 mg
Mercury (Hg) Content (Nom)	2 mg

Tornado T3

Energy Consumption kWh/1000 h	32 kWh
Product Data	
Order product name	Tornado T3 32W WW E27 220-240V 1PF/6
Full product name	Tornado T3 32W WW E27 220-240V 1PF/6
Full product code	872790087628400
Order code	87628400

Material Nr. (12NC)	929689301301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900876284
Numerator - Packs per outer box	6
EAN/UPC - Case	8727900876291

Dimensional drawing



Product	C (max)	D (max)	F (max)
Tornado T3 32W WW E27 220-240V 1PF/6	152.5 mm	74 mm	61 mm

