



# Tornado T3

## Tornado T3 32W CDL E27 220-240V 1PF/6

Tornado has outstanding brightness which makes your colors appear more Vivid. It allows easy replacement of high wattage of incandescent lamps.

### Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

### Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	8,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	8,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	2,160 lm
Color Designation	Cool Daylight
Chromaticity Coordinate X (Nom)	313
Chromaticity Coordinate Y (Nom)	337
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	80
Operating and Electrical	
Line Frequency	50 or 60 Hz


Input Frequency	50 or 60 Hz
Power Consumption	32.0 W
Lamp Current (Nom)	140 mA
Starting Time (Nom)	0.3 s
Warm-up time to 60% light	5-40 s s
Power Factor (Fraction)	0.95
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	Spiral
Approval and Application	
Mercury (Hg) Content (Max)	2.5 mg
Mercury (Hg) Content (Nom)	2 mg

Tornado T3

Energy Consumption kWh/1000 h	32 kWh
Product Data	
Order product name	Tornado T3 32W CDL E27 220-240V 1PF/6
Full product name	Tornado T3 32W CDL E27 220-240V 1PF/6
Full product code	872790087630700
Order code	87630700

Material Nr. (12NC)	929689301404
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900876307
Numerator - Packs per outer box	6
EAN/UPC - Case	8727900876314

Dimensional drawing



Product	D (max)	C (max)	F (max)
Tornado T3 32W CDL E27 220-240V 1PF/6	74 mm	152.5 mm	61 mm

