



TORNADO

TORNADO 15W WW E27 220-240V 1PF/6

The Helix range is a twist-shape compact fluorescent lamp, with optimal light distribution. It is available in 11W, 15W, 20W and 23W (25W), with lumen equivalence of 60W, 75W, 100W and 125W incandescent light bulb. It is also available in two color temperatures: warm white (2700K) and cool daylight (6500K). It is available in both 220-240V and 120-127V and able to operate under a wide voltage range (Power supply fluctuation). It consumes up to 80% less energy than the incandescent light bulb and lasts for 3 years.

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Product data


General Information		Correlated Color Temperature (Nom)	
Cap-Base	E27 [E27]	2700 K	
Nominal lifetime	8,000 h	Luminous Efficacy (rated) (Nom)	
Switching Cycle	5,000	65 lm/W	
Rated Lifetime (Hours)	8,000 h	Color rendering index (CRI)	
Lighting Technology	Compact Fluorescent Integrated	82	
Light Technical		LLMF At End Of Nominal Lifetime (Nom)	
Color Code	827 [CCT of 2700K]	70 %	
Luminous Flux	950 lm	Operating and Electrical	
Color Designation	Warm White (WW)	Line Frequency	50 or 60 Hz
Chromaticity Coordinate X (Nom)	463	Input Frequency	50 or 60 Hz
Chromaticity Coordinate Y (Nom)	420	Power Consumption	15 W
		Lamp Current (Nom)	110 mA
		Starting Time (Nom)	0.3 s
		Power Factor (Fraction)	0.6

TORNADO

Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	Spiral
Approval and Application	
Energy Consumption kWh/1000 h	15 kWh
Product Data	
Order product name	TORNADO 15W WW E27 220-240V 1PF/6

Full product name	TORNADO 15W WW E27 220-240V 1PF/6
Full product code	871829113803700
Local code description	TND15WWWES
Order code	929689848105
Material Nr. (12NC)	929689848105
Local order code	TND15WWWES
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291138037
Numerator - Packs per outer box	6
EAN/UPC - Case	8718291138044

Dimensional drawing



Product	D (max)	C (max)	F (max)
TORNADO 15W WW E27 220-240V 1PF/6	51.5 mm	107.5 mm	42.5 mm

