

PHILIPS

Smart Plug

Smart Accessory

Type B

With 1 socket

Control with app or voice



046677562342



Smart lighting for your daily living

Make any standard wall socket smart with this Philips Wi-Fi Smart Plug. Place the smart plug in a socket. Then, plug in a light or device to control with the WiZ app. Philips Wi-Fi bulbs are WiZ-connected. Not compatible with Philips Hue.

Easy setup

- Easy plug and play. Works with your existing Wi-Fi.

Smart control

- Control anywhere with your smartphone.
- Voice control via Google Assistant, Alexa and Siri.

Smart devices

- Automate your device with schedules
- Make ordinary devices smart: lamps, fans and more.

Highlights

Easy plug and play



WiZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new plug, download the WiZ app and you're ready to go!

Control from anywhere



Control your devices wherever you are with smartphone. No need to worry if you've left your devices on before leaving home. WiZ app is available for iOS and Android.

Go hands-free with voice control



Get hands-free control and use your voice instead. With voice-activated devices from Google and Amazon or use Siri shortcuts, you can control your devices with just the sound of your voice

Automate your device with schedules



Schedule your device to turn on / off to fit your daily routine and save energy

Make ordinary devices smart



Control ordinary lamps, decorative lights, fans, coffee machine and more. Works with devices that only need power on to function

Specifications

Design and finishing

- Color: white
- Material: plastic

Extra feature/accessory incl.

- Plug Type: USA, Canada, Taiwan, Columbia, Mexico, Honduras, Parama, Belize, Costa Rica, El Salvador, Guatemala
- Detection Area: 3m / 120 degree

Interactivity

- Current (A): 15

Power consumption

- Voltage: 125 V

Product dimensions & weight

- Height: 2.9 cm
- Length: 7.3 cm
- Net weight: 0.067 kg
- Width: 4.1 cm

Rated values

- Rated power: Max 1875 W

Service

- Warranty: 1 year(s)

Technical specifications

- IP code: UL01 – Dry Location (North America)
- Class of protection: UL earthed

Packaging dimensions and weight

- EAN/UPC – product: 046677562342
- Net weight: 0.090 kg
- Gross weight: 0.230 kg
- Height: 16.000 cm
- Length: 7.000 cm
- Width: 7.000 cm
- Material number (12NC): 929002446803



Issue date: 2023-11-08
Version: 0.18

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com