

PHILIPS

Bulb

LED

9W-65W

E26

Soft White

046677576561



State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Light beyond illumination

- Instant on

Highlights

Instant on

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional reflector
- Socket: E26
- Technology: LED
- Type of glass: Frosted

Bulb dimensions

- Height: 13 cm
- Weight: 0.075 kg
- Width: 9.5 cm

Durability

- Average life (at 2.7 hrs/day): 11 year(s)
- Lumen maintenance factor: 70%
- Nominal lifetime: 11,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 110 degree(s)
- Color consistency: ANSI
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Soft White
- Nominal luminous flux: 650 lumen
- Starting time: <0.5 s
- Warm-up time to 60% light: Instant full light
- Color Code: 827 | CCT of 2700K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Lamp current: 125 mA
- Efficacy: 72 lm/W

Packaging information

- EAN: 046677576561
- EOC: 576561
- Product title: 9BR30/LED/827/FR/P/ND 4/3CT

Power consumption

- Energy Star Certified: No
- Power factor: 0.5
- Voltage: 120 V
- Wattage: 9 W
- Wattage equivalent: 65 W

Product dimensions & weight

- Length: 13 cm

Rated values

- Rated beam angle: 110 degree(s)
- Rated lifetime: 11,000 hour(s)
- Rated luminous flux: 650 lumen
- Rated power: 9 W

Technical specifications

- Frequency: 60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 046677576561
- Net weight: 0.216 kg
- Gross weight: 0.294 kg
- Height: 17.900 cm
- Length: 9.500 cm
- Width: 18.500 cm
- Material number (12NC): 929001947993



Issue date: 2022-07-21
Version: 0.50

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com