




Complete fixture consists of Reflector Trim & Frame-in Kit. Select each separately.

Reflector Trim		CFL Frame-in Kit		Lamp	Ballast
1001HCLC	Clear Lens	NON-IC	1001F13N120	1-13W QT/TTT	Electronic
	Specular Clear	NON-IC	1001F13N347	1-13W QT/TTT	Electronic
	Clear Diffuse	NON-IC	1001F18N120	1-18W TTT	Electronic
	White	NON-IC	1001F18N347	1-18W TTT	Electronic
1001HCLF	Fresnel Lens	NON-IC	1003RF18N120	1-18W TTT	Electronic
	Specular Clear	NON-IC	1003RF18N347	1-18W TTT	Electronic
	Clear Diffuse	NON-IC	1001F18SE120	1-18W TTT	Dimming Lutron SE 5%
	White	NON-IC	1001F18MX120	1-18W TTT	Dimming Advance Mark10
1001HWHF	Opal Lens	NON-IC	1001F18M7120	1-18W TTT	Dimming Advance Mark7
	Specular Clear	NON-IC	1001F18HD120	1-18W TTT	Dimming HDF
	Clear Diffuse	NON-IC	1001F26N120	1-26W TTT	Electronic
	White	NON-IC	1001F26N347	1-26W TTT	Electronic
1001HCLO	IC / AirSeal®	NON-IC	1003RF26N120	1-26W TTT	Electronic
		NON-IC	1003RF26N347	1-26W TTT	Electronic
		NON-IC	1001F26SE120	1-26W TTT	Dimming Lutron SE 5%
		NON-IC	1001F26HL120	1-26W TTT	Dimming Lutron Hi-Lume 1%
1001HCDO	IC / AirSeal®	NON-IC	1001F26TW120	1-26W TTT	Dimming Lutron Tu-Wire 5%
		NON-IC	1001F26MX120	1-26W TTT	Dimming Advance Mark10
		NON-IC	1001F26M7120	1-26W TTT	Dimming Advance Mark7
		NON-IC	1001F26HD120	1-26W TTT	Dimming HDF
1001HWHO	IC / AirSeal®	NON-IC	1004ICXF13N120	1-13W QT/TTT	Electronic
		NON-IC	1004ICXF18N120	1-18W TTT	Electronic
		NON-IC	1004ICXF26N120	1-26W TTT	Electronic
		NON-IC	1004ICXF26MX120	1-26W TTT	Dimming Advance Mark10

Features

Reflector: Formed aluminum. Integral white flange.

Acrylic Lens Type:

C = Clear Lens
O = Opal Lens
F = Fresnel Lens

Markings

cCSAus certified; suitable for damp or wet locations.

Mounting / Ceiling opening

Note: For complete Frame-in Kit specifications, see spec sheet 1001F, 1004ICXF or 1003RF.

Job Information

Type:

Job Name:

Cat. No.:

Lamp(s):

Notes:

Lightolier

631 Airport Road, Fall River, Ma02720 • (508) 679-8131 • Fax (508) 674-4710
We reserve the right to change details of design, materials and finish.
© 2007 Philips Group

Lightolier is a Philips group brand

www.lightolier.com


Canlyte

3015 Louis-Amos, Lachine, Québec H8T 1C4 - (514) 636-0670 - (514) 636-0460


www.canlyte.com

PHILIPS

26W TRIPLE TUBE LAMP, LUMEN RATING = 1710 LMS, ELECTRONIC BALLAST, CL FINISH TRIM WITH CLEAR LENS



26W TRIPLE TUBE LAMP, LUMEN RATING = 1710 LMS, ELECTRONIC BALLAST, CL FINISH TRIM WITH FRESNEL LENS



26W TRIPLE TUBE LAMP, LUMEN RATING = 1710 LMS, ELECTRONIC BALLAST, CL FINISH TRIM WITH OPAL LENS

