

LIGHTOLIER

by  Signify

Downlighting

Calculite LED

VP Vandal proof trim



Experience the change, see the difference

Architectural decorative vandal proof ring combines the impact resistance you need with aesthetics you want.

Benefits

Calculite's vandal proof trim accessory is strength with a decorative feel. The sleek machined aluminum ring provides aesthetics fit for architectural spaces while providing the rigidity and impact resistance needed for the most demanding applications. The solid aluminum construction with clear polycarbonate lens lock in place to deter tampering, and provide Calculite trims with an IK10 impact rating.

VP Calculite LED

Vandal proof trim downlighting



Features

Apertures: 4" & 6" round
Finish: White
Reflectors: Suitable for use with any finish (must use flangeless trim option)
Lumens: 4" in 500–3000lm; 6" in 1000–6000lm
Construction: Machined alluminum. 9034HO Lexan optical grade polycarb lens
Impact Protection: IK10 (20 joule impact protection).
Ingress Protection: IP65, suitable for wet locations
Locking: Locks in place with discrete setscrew located on side of the ring
Installation: Mounted to frame with hardware, bayonet style twist on trim installation

Frame Complete luminaire = Frame + Engine + Trim

example: **C4RNLC**

Series	Aperture	Installation	Options
C4 Calculite LED 4"	R Round	N New construction (Non-IC) R Remodeler (Non-IC)	— Universal 120/277V (specify for Power Over Ethernet) 3 347V 3IP 347V w/Interact Pro LC Chicago Plenum IP Interact Pro EM Emergency
C6 Calculite LED 6"		A AirSeal (IC)	— N/A

Engine

example: **C4L15835NZ10U**

Series	Aperture	CRI	CCT	Beam	Dimming	Options
C4 Calculite LED 4"	05 500lm 10 1000lm 15 1500lm	20 2000lm 25 2500lm 30 3000lm	8 80CRI 9 90CRI	27 2700K 30 3000K 35 3500K 40 4000K	N Narrow M Medium W Wide	Z10 0–10V 1% D Dali L Lutron EcoSystem (Other controls options available, see specification sheets for details.)
C6 Calculite LED 6"	10 1000lm 15 1500lm 20 2000lm 25 2500lm	35 3500lm 48 4800lm 60 6000lm				U Universal (120/277/347V)

Trim

example: **C4RDLCCF**

Series	Aperture	Style	Finish	Flange
C4 Calculite LED 4"	R Round	DL Downlight WW Open Wall Wash LW Lensed Wall Wash CW Corner Wall Wash DW Double Wall Was	CL Specular clear CC Comfort clear CD Comfort clear diffuse CZ Champagne bronze BK Black (matte) WH White (matte)	F Flangeless
C6 Calculite LED 6"				

* Impact Protection Rating is a scale of 0–10 used to measure a product's ability to withstand physical impact.



Visit [Signify.com/warranties](https://www.signify.com/warranties) for more information on Signify's standard 5-year limited warranty.

See Calculite LED specification sheets for additional drawings and technical information.

