

Day-Brite

CFI

by  Signify

Healthcare

Multi-Med LED 2x2

Patient room luminaire



Day-Brite / CFI Multi-Med patient room exam luminaire provides the essential illumination requirements for examination lighting. The optical compartments are designed for efficient performance and patient comfort. The overall clean appearance of Multi-Med helps it blend into the ceiling plane and helps the environment feel less clinical. The standard anti-microbial finish and lens support a healthcare facility's infection-control efforts.

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Ordering guide

Example: ME221G35L940HSTDST101UNVDIM

Family	Size/Function	Ceiling Type	Exam Lumens	Color	Housing Material	Frame Material	Exam Optic
ME	221				HST	DST	
ME Multi-Med	221 2x2 Exam	G Grid/Surface F Flange	26L 2600 nominal delivered lumens 35L 3500 nominal delivered lumens 43L 4300 nominal delivered lumens 52L 5200 nominal delivered lumens 61L 6100 nominal delivered lumens 70L 7000 nominal delivered lumens	935 90 CRI, 3500K 940 90 CRI, 4000K 950 90 CRI, 5000K	HST 20 gauge CRS	DST 18 gauge CRS	101 .125 Opal Polycarbonate
Voltage		Driver		Options			
UNV Universal Voltage, 120-277 volt		DIM 0-10V dimming		EMLED¹ 10W Integral Emergency TR Tamper Resistant Torx Head Screws RF Radio Interference Filter LN35 LED Night Light, 3500K			

Footnotes

1 10W emergency battery pack w/ factory installed switch/test light in exam section, 1100lm nominal.



ME221 Multi-Med LED luminaire 2x2

Patient room luminaire

Features

- Opal polycarbonate lens provides even distribution of light.
- Antimicrobial finish on exposed surfaces designed to inhibit the growth of microbes.
- Optional LED night/chart light with integral switch to adjust light levels to 100/70/40 or 10%. Night light integrated into the exam section.

Specifications

- Construction: 20 gauge cold rolled steel housing.
- Door Frame: 18 gauge cold rolled steel frame.
- Reflector and Lenses: The luminaire has an opal polycarbonate lens which helps prevent incursion of particles.
- Finish: The housing, reflectors, and door frame are painted after fabrication with a white polyester powder coat paint finish. Exposed components are finished with antimicrobial paint.
- Electrical: Electronic drivers are universal 120-277V.
- Installation: Multi-Med can be installed into a suspended grid (G), surface mounted (G), or in drywall ceilings (F).
- Listing: cETLus listed for damp locations.
- Warranty: 5 year limited warranty.


Energy data

Lumen Package	LED Rows	Wattage	Delivered Lumens
26L	3Rows	37.5	2625
35L	4Rows	50.0	3500
43L	5Rows	62.5	4375
52L	6Rows	75.0	5250
61L	7Rows	87.5	6125
70L	8Rows	100.0	7000

ME221 Multi-Med LED luminaire 2x2

Patient room luminaire

Dimensions



Buy American Act of 1933 (BAA):

This product is manufactured in one of our US factories and, as of the date of this document, this product was considered a commercially available off-the-shelf (COTS) item meeting the requirements of the BAA. This BAA designation hereunder does not address (i) the applicability of, or availability of a waiver under, the Trade Agreements Act, or (ii) the "Buy America" domestic content requirements imposed on states, localities, and other non-federal entities as a condition of receiving funds administered by the Department of Transportation or other federal agencies. Prior to ordering, please visit www.signify.com/baa to view a current list of BAA-compliant products to confirm this product's current compliance.



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
 200 Franklin Square Drive,
 Somerset, NJ 08873
 Telephone 855-486-2216

Signify Canada Ltd.
 281 Hillmount Road,
 Markham, ON, Canada L6C 2S3
 Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.