

PHILIPS

Spiral energy saving
bulb

Tornado

12 W (60 W)

E14 cap

Warm white

8718291731337



Maximum brightness for increased comfort

Philips Tornado energy-saving bulbs provide instant brightness and make colors appear more vivid. Due to its compact design, this low-consumption spiral bulb fits almost anywhere, saving energy and money for up to 8 years.

Sustainable choice

- Carbon footprint
- Save energy from the moment you turn the switch

Beacon of trust

- You can trust what the Philips packaging is saying

Saves energy and money

- Long lifetime – lasting up to 8 years

Highlights

Carbon footprint

Energy savers reduce the amount of energy in your home, which not only results in a lower energy bill, but also in less carbon (CO₂) output by your energy supplier. Together we make this a better world to live in.

Energy efficient

All Philips energy savers save energy from the moment you turn the switch. During their lifetime they use fewer kW and thus also result in a lower energy bill. The level of energy saving differs per lamp type and technology.

Reliable quality

Philips keeps its promises about lamp performance. You can trust what the Philips packaging is saying about light output, lifetime and wattage equivalent to incandescent lamps.

Long lifetime - up to 8 years



Philips energy-saving bulbs are designed to last. With a lifetime of up to 8 years, you can avoid the hassle and cost of frequently replacing bulbs, while saving energy year in, year out.

Specifications

Bulb characteristics

- Shape: Spiral
- Dimmable: No
- Socket: B22

Bulb dimensions

- Height: 91 mm
- Width: 46 mm

Durability

- Average life (at 2.7 hrs/day): 8 year(s)
- Nominal lifetime: 8,000 hour(s)

Light characteristics

- Application: Comfortable light
- Beam angle: not applicable degree(s)
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Warm White
- Nominal luminous flux: 741 lumen

Power consumption

- Voltage: 220-240 V
- Wattage: 12 W
- Wattage equivalent: 60 W

Rated values

- Rated peak intensity: not applicable cd

Packaging dimensions and weight

- EAN/UPC - product: 8718291731337
- Net weight: 0.050 kg
- Gross weight: 0.062 g
- Height: 9.700
- Length: 4.700
- Width: 4.700
- Material number (12NC): 929689888599



Issue date: 2023-11-08
Version: 0.399

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com