

PHILIPS

Downlight

Functional

MESON



8718696170953



Comfortable LED light that's easy on your eyes

Philips LED luminaires provide light that is designed for the comfort of your eyes.

Easy to experience

- Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

Light effect

- Bright light with uniform distribution

Safety

- No harmful UV radiation

Mounting

- Integrated driver with connector for easy installation.

Durability

- Long life span up to 15,000 hours

Highlights

Suitable for low ceilings Slim design Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

No harmful UV radiation

The product is designed to eliminate any potentially harmful UV radiation.

Integrated driver with connector for easy installation.

Allows for safe and easy installation with no knowledge or wiring required.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Design and finishing

- Color: white
- Material: plastic

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No
- Centerpiece: Yes

Light characteristics

- Beam angle: 110 degree(s)
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Functional

Product dimensions & weight

- Cut out length: 10.5 cm
- Cut out width: 10.5 cm
- Height: 4.7 cm
- Length: 12 cm
- Net weight: 0.077 kg
- Recessed distance: 10.1 cm
- Width: 12 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture: 640
- Light color: 4000
- Mains power: 220-240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 9
- IP code: IP20
- Class of protection: Class II

Packaging dimensions and weight

- EAN/UPC - product: 8718696170953
- Net weight: 0.055 kg
- Gross weight: 0.080 kg
- Height: 123.000 mm
- Length: 54.000 mm
- Width: 131.000 mm
- Material number (12NC): 915005747501



Issue date: 2022-07-21
Version: 0.60

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com