

PHILIPS

Ceiling light

Functional

StylEdge ceiling light

Cool Day light

10W, Round

8718699631574



Superior ceiling light and style

Decorative ceiling light and down light, made of high quality aluminium blends well on your ceiling enhancing the décor.

Match your interior

- Decorative metallic finishing

Light effect

- Bright light with uniform distribution

Material & finishing

- Durable aluminum housing

Durability

- Long life span up to 30,000 hours

Highlights

Decorative metallic finishing

Contemporary metallic finishing adds a modern touch.

Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Durable aluminum housing

Creates a strong, clean and contemporary style for your space.

Long life span up to 30,000 hours

Philips LED technology extends your product's lifetime up to 30,000 hours.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

Design and finishing

- Color: White
- Material: plastic

Durability

- Average life (at 2.7 hrs/day): 25 year(s)
- Lumen maintenance factor: 0.7
- Number of switch cycles: 10,000

Extra feature/accessory incl.

- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 120 degree(s)
- Color consistency: 5
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

Miscellaneous

- Especially designed for: Functional

Other characteristics

- Lamp current: 50 mA
- Efficacy: 90 lm/W

Power consumption

- Power factor: 0.9
- Voltage: 220-240 V

Product dimensions and weight

- Cut out length: 11 cm
- Cut out width: 11 cm
- Height: 4.7 cm
- Length: 12.1 cm
- Width: 12.1 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Diameter: 121 mm
- Total lumen output fixture: 900
- Light color: 6500
- Mains power: 220-240
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 10
- IP code: IP20

Packaging dimensions and weight

- EAN/UPC - product: 8718699631574
- Net weight: 0.140 kg
- Gross weight: 0.190 kg
- Height: 14.500 cm
- Length: 16.500 cm
- Width: 5.200 cm
- Material number (12NC): 929001951810



Issue date: 2023-11-08
Version: 0.50

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com