

PHILIPS

Bulb

LED

7W-9(50W GLS, 9W CFL)W

E27

White

8718699732882



State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.
- Contains no mercury

Highlights

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no

ultra-violet light means that fabric and items under this light won't fade.

Contains no mercury

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Type of glass: Frosted
- Bulb Finish: Frosted

Bulb dimensions

- Height: 10.8 cm
- Width: 6 cm

Durability

- Nominal lifetime: 25,000 hour(s)
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 150 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 500 lm
- Warm-up time to 60% light: instant full light
- Color Code: 830 | CCT of 3000K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 71 lm/W

Packaging information

- EAN: 8718699732882
- EOC: 871869973288200
- Product title: ESS LEDBulb 7W E27 3000K 230V1PF/12AFMM

Power consumption

- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 7 W
- Wattage equivalent: 9 W

Product dimensions and weight

- Length: 10.8 cm

Rated values

- Rated peak intensity: 107 cd

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718699732882
- Net weight: 0.06 kg
- Gross weight: 0.08 kg
- Height: 13.7 cm
- Length: 6.1 cm
- Width: 6.1 cm
- Material number (12NC): 929001955168



Issue date: 2024-02-02
Version: 0.34

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com