PHILIPS

Bulb

LED

10W-80(80W GLS, 15W CFL)W

B22

Cool Daylight

8718699747596




# State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

**Choose for a sustainable solution**

- You can trust what the Philips packaging is saying.
- Contains no mercury

# Highlights

**No UV or IR**
The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

**Contains no mercury**

# Specifications

### Bulb characteristics
- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: B22
- Type of glass: Frosted
- Bulb Finish: Frosted

### Bulb dimensions
- Height: 10.8 cm
- Width: 6 cm

### Durability
- Nominal lifetime: 15000 hour(s)
- Number of switch cycles: 50000

### Light characteristics
- Color rendering index (CRI): 70
- Color temperature: 6500 K
- Nominal luminous flux: 950 lm
- Warm-up time to 60% light: instant full light
- Color Code: 765 | CCT of 6500K

### Miscellaneous
- EyeComfort: Yes

### Other characteristics
- Efficacy: 95 lm/W

### Packaging information
- EAN: 8718699747596
- EOC: 871869974759600
- Product title: ESS LEDBulb 10W B22 6500K 230V 1CT/48 PK

### Power consumption
- Power factor: 0.5
- Voltage: 220-240 V
- Wattage: 10 W
- Wattage equivalent: 80 W

### Product dimensions and weight
- Length: 10.8 cm

### Technical specifications
- Frequency: 50-60 Hz

### Packaging dimensions and weight
- EAN/UPC - product: 8718699747596
- Net weight: 0.06 kg
- Gross weight: 0.08 kg
- Height: 10.6 cm
- Length: 6.1 cm
- Width: 6.1 cm
- Material number (12NC): 929002344969

Issue date: 2024-02-02
Version: 0.19

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

**www.lighting.philips.com**