

PHILIPS

Ceiling light

Functional

Essential CL505

White

Wireless Dim

8719514266698



Set your desired ambiance at your fingertips

Philips LED luminaires provide light that is designed for the comfort of your eyes

Light effect

- Adjustable color temperature

Premium quality

- EyeComfort - light that's easy on the eyes

Control

- Convenient brightness control step dimming function (remote control included)

Durability

- Long life span up to 15,000 hours

Highlights

Adjustable color temperature

Shift seamlessly from cool white light for concentration to a more cozy glow to unwind in.

Eyecomfort

Poor quality light can cause eye strain. With many of us spending time indoors, it's more important than ever to properly light your home. Our products meet stringent test criteria including flicker, strobe, glare, color rendition and dimming effects to ensure they meet EyeComfort requirements. Philips LED bulbs not only deliver comfortable light, but also stay that way for the duration of their lifespan, delivering consistent light quality, output, and color for more than a decade. Switch to light that's easy on your eyes. Your eyes will thank you.

Convenient brightness control step dimming function (remote control included)

Shift between different levels of brightness to match your mood or activity.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Design and finishing

- Color: white
- Material: metal/plastic

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: Yes
- LED integrated: Yes
- Remote control included: Yes
- Centerpiece: Yes

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Functional

Product dimensions & weight

- Height: 8.7 cm
- Length: 40 cm
- Net weight: 0.84 kg
- Width: 40 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 400 mm
- Total lumen output fixture: 2000
- Light color: 6500/4000/2700
- Mains power: 220-240
- Fixture dimmable: Yes
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 23
- IP code: IP20
- Class of protection: Class I

Packaging dimensions and weight

- EAN/UPC - product: 8719514266698
- Net weight: 0.840 kg
- Gross weight: 1.236 kg
- Height: 43.800 cm
- Length: 9.300 cm
- Width: 43.500 cm
- Material number (12NC): 929002562407



Issue date: 2021-11-29
Version: 0.44

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com