

PHILIPS

USB Charger

Switches & Sockets

LeafStyle

Polycarbonate

Mettalic Black

8719514298675



High quality switch and socket designed to safely last for years

Philips LeafStyle provides modern design, high safety standard and easy to install switch & socket to your family.

Convenience

- USB charging 2.0A

Safety and Durability

- Safety and Durability

Easy for use

- Compatible with other brands
- Easy for use, save time and energy
- Modular design, free combination, follow your desire

Modern Design

- Modern design, more than a functional part, it is a decoration

Highlights

USB charging 2.0A

Suitable for iPad, iPhone & Android Phone. Fast charging due to 2A power output.

Safety and Durability

1. High quality PC for Cover and Base.
2. Key metal parts are used with 0.6mm thickness phosphor bronze.
3. Pass IEC standard and follow more strict Philips internal design rule.

Compatible with other brands

Compatible with main stream modular switch in other brands.

Easy for use

1. Smaller module height, which will make installation more easy.
2. Quick installation terminal, no need to use screw.

Modular design

Choose modules and combine on one cover to meet personal preference.

Modern Design

1. The inspiration of our design is the natural curve of leaf, could be an art decoration for your home.
2. Two classic colors -- white and metallic black to match various home styles.

Specifications

Design and finishing

- Color: black
- Material: PC
- Module/Gang: 1 Module
- Socket/connector Type: USB
- Product Range: LeafStyle
- Minimum Installation Box Depth: 34 cm

Durability

- Number of Operation Cycles: 3,000

Interactivity

- Output Current: 2.4 A

Other characteristics

- Installation Type: Screwed Installation

Power consumption

- Voltage: 220 V
- Output voltage: 5 V

Product dimensions & weight

- Length: 4.59 cm
- Width: 4.4 cm
- Depth: 4.17 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8719514298675
- Net weight: 0.051 kg
- Gross weight: 0.052 kg
- Height: 4.200 cm
- Length: 4.400 cm
- Width: 4.600 cm
- Material number (12NC): 913713879501



Issue date: 2022-07-21
Version: 0.263

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com