

PHILIPS

Filament Bulb Frosted
100W A60 E27

LED

10.5W-100W

E27

Warm Glow

Dimming



8719514324114



Experience dimmable, warm white LED light

Philips LED light bulbs provide a beautiful, warm white light, an exceptionally long life and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your frosted traditional bulbs.

Choose for a sustainable solution

- Better for your wallet and your planet

Create the right light for your home

- Perfect for general room lighting

Highlights

Energy savings of up to 90%

LED technology provides energy savings of up to 90% compared with your standard bulb. It therefore pays for itself and saves you money year after year. It also helps to protect the environment.

Perfect for general lighting



Modern lighting with Philips LED standard bulbs for all-around illumination, perfect for general room lighting.

Specifications

Bulb characteristics

- Dimmable: Only with specific dimmers
- Intended use: Indoor
- Lamp shape: Non-directional bulb
- Socket: E27
- Type of glass: Frosted
- Lamp Finish: Frosted
- Bulb material: Glass

Lamp dimensions

- Height: 10.8 cm
- Width: 6 cm

Design and finishing

- Material: Glass

Durability

- Nominal lifetime: 15,000 h
- Number of switch cycles: 20,000

Light characteristics

- Colour rendering index (CRI): 90
- Colour temperature: 2200–2700 K
- Nominal luminous flux: 1521 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 922-927 | CCT of 2200K-2700K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 144 lm/W

Packaging information

- EAN: 8719514324114
- EOC: 871951432411400
- Product title: LED classic 100W A60 E27 FR WGD90 SRT4

Power consumption

- Power factor: 0.9
- Voltage: 220–240 V
- Wattage: 10.5 W
- Wattage equivalent: 100 W
- Energy efficiency label (EEL): D

Product dimensions and weight

- Length: 10.8 cm

Technical specifications

- Frequency: 50–60 Hz
- EPREL registration number: 453260

The bulb

- Colour consistency: 6

Packaging dimensions and weight

- EAN/UPC – product: 8719514324114
- Net weight: 0.03 kg
- Gross weight: 0.05 kg
- Height: 14.6 cm
- Length: 6.5 cm
- Width: 6.3 cm
- Material number (12NC): 929003011701



Issue date: 2024-02-02
Version: 0.252

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com