

PHILIPS

Filament Candle
Clear 25W B35 E14

LED

2.5 W-25 W

E14

Warm Glow

Dimming



8719514324152



Experience dimmable, warm white LED light

Philips LED clear candles provide a beautiful, sparkling light effect and an exceptionally long life. Beautiful both switched on and switched off, this light bulb is the perfect match for chandelier fixtures with small (E14) fittings.

Choose for a sustainable solution

- Better for your wallet and your planet

Create the right light for your home

- Perfect for decorative fixtures

Highlights

Energy savings of up to 90%

LED technology provides energy savings of up to 90% compared with your standard bulb. It therefore pays for itself and saves you money year after year. It also helps to protect the environment.

Perfect for decorative fixtures



Modern lighting in Philips LED candles for use in decorative fixtures, such as in chandeliers, ceiling fans, vanity strips and post lights.

Specifications

Bulb characteristics

- Dimmable: Only with specific dimmers
- Intended use: Indoor
- Lamp shape: Non-directional candle
- Socket: E14
- Type of glass: Clear
- Lamp Finish: Clear
- Bulb material: Glass

Lamp dimensions

- Height: 9.7 cm
- Width: 3.5 cm

Design and finishing

- Material: Glass

Durability

- Nominal lifetime: 15,000 h
- Number of switch cycles: 20,000

Light characteristics

- Colour rendering index (CRI): 90
- Colour temperature: 2200–2700 K
- Nominal luminous flux: 340 lm
- Warm-up time to 60% light: Instant full light
- Colour Code: 922-927 | CCT of 2200K-2700K

Miscellaneous

- EyeComfort: Yes

Other characteristics

- Efficacy: 136 lm/W

Packaging information

- EAN: 8719514324152
- EOC: 871951432415200
- Product title: LED classic 25W B35 E14 CL WGD90 SRT4

Power consumption

- Power factor: 0.6
- Voltage: 220–240 V
- Wattage: 2.5 W
- Wattage equivalent: 25 W
- Energy efficiency label (EEL): D

Product dimensions and weight

- Length: 9.7 cm

Technical specifications

- Frequency: 50–60 Hz
- EPREL registration number: 1109136

The bulb

- Colour consistency: 6

Packaging dimensions and weight

- EAN/UPC - product: 8719514324152
- Net weight: 0.01 kg
- Gross weight: 0.03 kg
- Height: 14.6 cm
- Length: 4.6 cm
- Width: 6.3 cm
- Material number (12NC): 929003011999



Issue date: 2024-02-02
Version: 0.213

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com