PHILIPS

Bulb

LED

7W-60W

E27

Warm White

8719514327542




# A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

### High quality light
- No visible flicker

### Choose for a sustainable solution
- You can trust what the Philips packaging is saying.

### Create the right light for your home
- A simple LED for everyday use

# Highlights

### No visible flicker
When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

### No UV or IR
The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

### A Simple LED for Everyday Use
The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

# Specifications

### Bulb characteristics
- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27

### Bulb dimensions
- Height: 10.4 cm
- Width: 6 cm

### Durability
- Nominal lifetime: 15,000 h
- Number of switch cycles: 30,000

### Light characteristics
- Beam angle: 300 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Nominal luminous flux: 806 lm
- Warm-up time to 60% light: instant full light
- Color Code: 827 | CCT of 2700K

### Miscellaneous
- EyeComfort: Yes

### Other characteristics
- Efficacy: 115 lm/W

### Packaging information
- EAN: 8719514327542
- EOC: 871951432754200
- Product title: LED classic 7-60W A60 E27 WW CL ND AU

### Power consumption
- Power factor: 0.51
- Voltage: 220-240 V
- Wattage: 7 W
- Wattage equivalent: 60 W

### Product dimensions and weight
- Length: 10.4 cm

### Technical specifications
- Frequency: 50-60 Hz

### Packaging dimensions & weight
- EAN/UPC - product: 8719514327542
- Net weight: 0.03 kg
- Gross weight: 0.06 kg
- Height: 12 cm
- Length: 6.6 cm
- Width: 6.6 cm
- Material number (12NC): 929001387376

Issue date: 2024-02-02
Version: 0.40

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

**www.lighting.philips.com**