

PHILIPS

Ceiling light

LED ceiling fan light

Bliss

White



8719514334441



One fixture. Your switch. Three light settings.

Combine customizable light with a comfortable breeze with the Philips LED retractable ceiling fan light, which includes a remote control. With transparent blades that retract out of sight when not in use and three SceneSwitch light settings, this light creates the perfect atmosphere in any space.

Easy to experience

- Retractable ceiling fan with transparent blades
- Easy to install, safe to use
- Powerful, reliable performance

Ambient light effect

- Bright yet comfortable ceiling light

Premium quality

- Quiet motor

Control

- The remote control offers easy control of all the functions of the ceiling fan and light. Switch the light or fan on or off, choose from three fan speeds, cycle through SceneSwitch light settings, use the flashlight feature, or set one of five timers.

Mounting

- Easy to install, safe to use

Highlights

Retractable ceiling fan with transparent blades

Say goodbye to spinning shadows on the ceiling: this fan has transparent blades that can be folded into the light and out of sight when not in use.

Easy to install, safe to use

The Philips LED retractable ceiling fan light has passed strict safety testing and includes drop-resistant screws and a sturdy design alongside other important safety features.

Powerful, reliable performance

The Philips LED retractable ceiling fan light was designed to ensure powerful air circulation and continued reliability over time. Use it alone or with air conditioning for faster cooling.

Bright yet comfortable ceiling light

The Philips LED retractable ceiling fan light offers powerfully bright — yet comfortable — light for your home, which you can control with the included remote control or a wall switch.

Quiet motor

The Philips LED retractable ceiling fan light offers a quiet motor, circulating the air in the room without any loud noises.

Remote control included

The remote control offers easy control of all the functions of the ceiling fan and light. Switch the light or fan on or off, choose from three fan speeds, cycle through SceneSwitch light settings, use the flashlight feature, or set one of five timers.

Easy to install, safe to use

The Philips LED retractable ceiling fan light has passed strict safety testing and includes drop-resistant screws and a sturdy design alongside other important safety features.

Specifications

Design and finishing

- Color: white
- Material: metal/plastic

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: Yes
- Centerpiece: Yes

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Functional

Product dimensions & weight

- Height: 41.8 cm
- Length: 51 cm
- Net weight: 7.8 kg
- Width: 51 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 510 mm
- Total lumen output fixture: 4500
- Light color: 5500-3000-4000
- Mains power: 220-240
- Fixture dimmable: No
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 45+35
- IP code: IP20
- Class of protection: Class I

Packaging dimensions and weight

- EAN/UPC - product: 8719514334441
- Net weight: 7.800 kg
- Gross weight: 10.820 kg
- Height: 30.000 cm
- Length: 55.300 cm
- Width: 55.300 cm
- Material number (12NC): 929002681501



Issue date: 2023-01-06
Version: 0.396

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com