

PHILIPS

Pillar double spotlight

Hue White ambiance

Includes GU10 LED bulb

Bluetooth control via app

Includes dimmer switch

Add Hue Bridge to unlock more



8719514338463



Easy smart lighting

Use the Philips Hue White ambiance Pillar double spot light in white to get warm-to-cool white light in any room of your home. Control instantly with Bluetooth or the included Hue dimmer switch or unlock the full suite of smart lighting features with the Philips Hue Bridge.

Comfort dimming

- Pair with a wireless dimmer switch for easy wireless control


Easy smart lighting

- Control up to 10 lights with the Bluetooth app
- Control lights with your voice*
- Set the right mood with warm to cool white light
- Get the perfect light recipes for your daily activities
- Unlock the full suite of smart lighting features with the Bridge



Highlights

Installation free dimming



Control your Philips Hue lights directly with the wireless dimmer switch. You can turn the lights on and off, switch between the four different light recipes and dim to the right brightness. Installation is quick, simple and hassle-free. All you have to do is pair the switch with the lamp and place the switch anywhere in your home. It's that easy.

Control up to 10 lights with the Bluetooth app



With the Hue Bluetooth app, you can control your Hue smart lights in a single room of your home. Add up to 10 smart lights and control them all with just the touch of a button on your mobile device.

Control lights with your voice*



Philips Hue works with Amazon Alexa and the Google Assistant when paired with a compatible Google Nest or Amazon Echo device. Simple voice commands allow you to control multiple lights in a room or just a single lamp.

Set the right mood with warm to cool white light



These bulbs and light fixtures offer different shades of warm to cool white light. With complete dimmability from bright to low nightlights, you can tune your lights to the perfect shade and brightness of light for your daily needs.

Get the perfect light recipes for your daily activities



Make your day easier and more pleasant with four preset light recipes handcrafted especially for your daily tasks: Energize, Concentrate, Read, and Relax. The two cool-toned scenes, Energize and Concentrate, help you get going in the morning or keep your focus, while the warmer scenes of Read and Relax help support comfortable reading or calm a busy mind.

Unlock the full suite of smart lighting features with the Bridge



The Bridge unlocks the features that make smart lighting truly smart — away-from-home control, voice control, automated lighting, and much more. Add a Bridge to your setup to create immersive experiences, tap into technology that's secure and reliable, and more. The Bridge is the key to smart lighting like you've never seen before.

Specifications

Design and finishing

- Color: White
- Material: Metal

Extra feature/accessory incl.

- 4 light recipes: Yes
- Adjustable spot head: Yes
- Dimmable with Hue app and switch: Yes
- Dimmable with remote control: Yes
- Hue Switch: Yes
- Hue Switch Included: Yes
- LED lamp(s) included: Yes
- Perfectly suited for ambiance creation: Yes
- Upgradeable with Philips HUE bridge: Yes
- ZigBee Light Link: Yes

Miscellaneous

- Especially designed for: Living- & Bedroom
- Style: Contemporary
- Type: Spot Light
- EyeComfort: No

Product dimensions and weight

- Net weight: 1.775 kg
- Height: 12 cm
- Length: 19.3 cm
- Width: 10.3 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lumen output at 4000K: 700 lm
- Lifetime up to: 15,000 hour(s)
- Total lumen output fixture (hidden): 700 lm
- Lumen output bulb included: 350 lm
- Light source equivalent to traditional bulb of: 50 W
- Total lumen output fixture: 700 lm
- Bulb technology: LED, 230 V
- Light color: 2200-6500 Hue White Ambiance
- Mains power: 50-60 Hz
- LED: Yes
- Built in LED: No
- Number of bulbs: 2
- Fitting/cap: GU10
- Wattage bulb included: 10 W
- Maximum wattage replacement bulb: 5.5 W
- IP code: IP20
- Class of protection: II – double insulated
- Replaceability of light source: Replaceable LED light source by end-user
- Lumen output at 2700K: 500 lm

What's supported

- Compatible with Effects: Yes
- Philips Hue App: IOS 15 and above, Android 10.0 and above

Packaging dimensions and weight

- EAN/UPC – product: 8719514338463
- Net weight: 2.03 kg
- Gross weight: 2.36 kg
- Height: 14 cm
- Length: 17.6 cm
- Width: 21.9 cm
- Material number (12NC): 929003046601



Issue date: 2024-02-02
Version: 0.392

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com