

# PHILIPS

Cher suspension  
light

Hue White ambiance

Integrated LED

Bluetooth control via app

Includes dimmer switch

Add Hue Bridge to unlock more



8719514341210



## Easy smart lighting

The Philips Hue White ambiance Cher pendant light in white offers warm-to-cool white light to help you Read, Relax, Concentrate, and Energize throughout your day. Control instantly with the included Hue dimmer switch or Bluetooth or add a Hue Bridge to unlock even more smart lighting features.

### Comfort dimming

- Pair with a wireless dimmer switch for easy wireless control


### Easy smart lighting

- Control up to 10 lights with the Bluetooth app
- Control lights with your voice\*
- Set the right mood with warm to cool white light
- Get the perfect light recipes for your daily activities
- Unlock the full suite of smart lighting features with the Bridge



# Highlights

## Installation free dimming




Control your Philips Hue lights directly with the wireless dimmer switch. You can turn the lights on and off, switch between the four different light recipes and dim to the right brightness. Installation is quick, simple and hassle-free. All you have to do is pair the switch with the lamp and place the switch anywhere in your home. It's that easy.

## Control up to 10 lights with the Bluetooth app



With the Hue Bluetooth app, you can control your Hue smart lights in a single room of your home. Add up to 10 smart lights and control them all with just the touch of a button on your mobile device.

## Control lights with your voice\*



Philips Hue works with Amazon Alexa and the Google Assistant when paired with a compatible Google Nest or Amazon Echo device. Simple voice commands allow you to control multiple lights in a room or just a single lamp.

## Set the right mood with warm to cool white light



These bulbs and light fixtures offer different shades of warm to cool white light. With complete dimmability from bright to low nightlights, you can tune your lights to the perfect shade and brightness of light for your daily needs.

## Get the perfect light recipes for your daily activities



Make your day easier and more pleasant with four preset light recipes handcrafted especially for your daily tasks: Energize, Concentrate, Read, and Relax. The two cool-toned scenes, Energize and Concentrate, help you get going in the morning or keep your focus, while the warmer scenes of Read and Relax help support comfortable reading or calm a busy mind.

## Unlock the full suite of smart lighting features with the Bridge



The Bridge unlocks the features that make smart lighting truly smart — away-from-home control, voice control, automated lighting, and much more. Add a Bridge to your setup to create immersive experiences, tap into technology that's secure and reliable, and more. The Bridge is the key to smart lighting like you've never seen before.

# Specifications

## Design and finishing

- Color: White
- Material: Synthetic

## Extra feature/accessory incl.

- 4 light recipes: Yes
- Diffused light effect: Yes
- Dimmable with Hue app and switch: Yes
- Dimmable with remote control: Yes
- Hue Switch: Yes
- Hue Switch Included: Yes
- LED integrated: Yes
- Perfectly suited for ambiance creation: Yes
- Upgradeable with Philips HUE bridge: Yes
- ZigBee Light Link: Yes

## Miscellaneous

- Especially designed for: Living- & Bedroom
- Style: Modern
- Type: Suspension Lights
- EyeComfort: Yes

## Product dimensions and weight

- Net weight: 2.700 kg
- Height: 20.6 cm
- Height maximum: 175 cm
- Height minimum: 34 cm
- Length: 47.5 cm
- Width: 47.5 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Lumen output at 4000K: 2,900 lm
- Lifetime up to: 25,000 hour(s)
- Light source equivalent to traditional bulb of: 204 W
- Bulb technology: 24 V
- Light color: 2200-6500 Hue White Ambiance
- Mains power: 50-60 Hz
- Fixture dimmable: Yes
- LED: Yes
- Built in LED: Yes
- Energy class included light source: F
- Number of bulbs: 1
- Wattage bulb included: 24 W
- IP code: IP20
- Class of protection: I - earthed
- Replaceability of light source: Replaceable LED light source by a professional
- Replaceability of control gears: Replaceable control gear by a professional
- Lumen output at 2700K: 2,750 lm

## What's supported

- Compatible with Effects: Yes
- Philips Hue App: IOS 15 and above, Android 10.0 and above

## Packaging dimensions and weight

- EAN/UPC - product: 8719514341210
- Net weight: 2.7 kg
- Gross weight: 5.41 kg
- Height: 0
- Length: 0
- Width: 0
- Material number (12NC): 929003054201



Issue date: 2024-02-02  
Version: 0.387

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)