

# PHILIPS

## Flourish ceiling light

Hue White and color  
ambiance

Integrated LED

Bluetooth control via app

Control with app or voice\*

Add Hue Bridge to unlock more



8719514343504



## Easy smart lighting

Get powerful light for any occasion with the Flourish ceiling lamp, which allows you to set warm-to-cool and colored light. Works as a standalone light or as part of your smart lighting system with the Hue Bridge.

### Easy smart lighting

- Control up to 10 lights with the Bluetooth app
- Control lights with your voice\*
- Create a personalized experience with colorful smart light
- Set the right mood with warm to cool white light
- Get the perfect light recipes for your daily activities
- Unlock the full suite of smart lighting features with the Bridge



# Highlights

## Control up to 10 lights with the Bluetooth app



With the Hue Bluetooth app, you can control your Hue smart lights in a single room of your home. Add up to 10 smart lights and control them all with just the touch of a button on your mobile device.

## Control lights with your voice\*



Philips Hue works with Amazon Alexa and the Google Assistant when paired with a compatible Google Nest or Amazon Echo device. Simple voice commands allow you to control multiple lights in a room or just a single lamp.

## Create a personalized experience with colorful smart light



Transform your home with over 16 million colors, instantly creating the right atmosphere for any event. With the touch of a button, you can set a festive mood for a party, turn your living room into a movie theater, enhance your home decor with color accents, and much more.

## Set the right mood with warm to cool white light



These bulbs and light fixtures offer different shades of warm to cool white light. With complete dimmability from bright to low nightlights, you can tune your lights to the perfect shade and brightness of light for your daily needs.

## Get the perfect light recipes for your daily activities



Make your day easier and more pleasant with four preset light recipes handcrafted especially for your daily tasks: Energize, Concentrate, Read, and Relax. The two cool-toned scenes, Energize and Concentrate, help you get going in the morning or keep your focus, while the warmer scenes of Read and Relax help support comfortable reading or calm a busy mind.

## Unlock the full suite of smart lighting features with the Bridge



The Bridge unlocks the features that make smart lighting truly smart — away-from-home control, voice control, automated lighting, and much more. Add a Bridge to your setup to create immersive experiences, tap into technology that's secure and reliable, and more. The Bridge is the key to smart lighting like you've never seen before.

# Specifications

## Design and finishing

- Color: White
- Material: Glass

## Extra feature/accessory incl.

- Dimmable with Hue app and switch: Yes

## Miscellaneous

- Especially designed for: Living- & Bedroom, Home office & Study
- Style: Contemporary
- Type: Ceiling Lights
- EyeComfort: No

## Product dimensions and weight

- Net weight: 3.010 kg
- Height: 14.1 cm
- Length: 35.9 cm
- Width: 35.9 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Lumen output at 4000K: 2,250 lm
- Lifetime up to: 25,000 hour(s)
- Light source equivalent to traditional bulb of: 175 W
- Bulb technology: 24 V
- Light color: 2000-6500 Hue White Color Ambiance
- Mains power: 50-60 Hz
- LED: Yes
- Built in LED: Yes
- Energy class included light source: G
- Number of bulbs: 1
- Wattage bulb included: 32.5 W
- IP code: IP20
- Class of protection: I - earthed
- Replaceability of light source: Replaceable LED light source by a professional
- Replaceability of control gears: Replaceable control gear by a professional
- Lumen output at 2700K: 1,940 lm

## What's supported

- Compatible with Effects: Yes
- Philips Hue App: IOS 15 and above, Android 10.0 and above

## Packaging dimensions and weight

- EAN/UPC - product: 8719514343504
- Net weight: 3.01 kg
- Gross weight: 4.49 kg
- Height: 281 mm
- Length: 436 mm
- Width: 436 mm
- Material number (12NC): 929003053501



Issue date: 2024-02-02  
Version: 0.335

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)