

PHILIPS

Bulb

LED

11W-73(73W halogen,20W
CFL)W

E27

Cool Daylight

8719514359321



State-of-the-art LED light bulb for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.
- Contains no mercury

Highlights

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no

ultra-violet light means that fabric and items under this light won't fade.

Contains no mercury

Specifications

Bulb characteristics

- Dimmable: No
- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Type of glass: Frosted
- Bulb Finish: Frosted

Bulb dimensions

- Height: 10.8 cm
- Width: 6 cm

Durability

- Nominal lifetime: 10,000 h
- Number of switch cycles: 50,000

Light characteristics

- Beam angle: 150 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 6500 K
- Nominal luminous flux: 1250 lm
- Warm-up time to 60% light: instant full light
- Color Code: 865 | CCT of 6500K

Miscellaneous

- EyeComfort: No

Other characteristics

- Efficacy: 113 lm/W

Packaging information

- EAN: 8719514359321
- EOC: 871951435932100
- Product title: ESS LEDBulb 11W E27 6500K 230V 6CT/6 AU

Power consumption

- Power factor: 0.51
- Voltage: 220-240 V
- Wattage: 11 W
- Wattage equivalent: 73 W

Product dimensions and weight

- Length: 10.8 cm

Rated values

- Rated peak intensity: 248 cd

Technical specifications

- Frequency: 50-60 Hz

Packaging dimensions & weight

- EAN/UPC - product: 8719514359321
- Net weight: 0.22 kg
- Gross weight: 0.24 kg
- Height: 11.5 cm
- Length: 18.6 cm
- Width: 12.4 cm
- Material number (12NC): 929002299896



Issue date: 2024-02-02
Version: 0.19

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com