

# PHILIPS

Ceiling light

LED ceiling fan light

Bliss

White



8719514408494



## One fixture. Your switch. Three light settings.

Combine customizable light with a comfortable breeze with the Philips LED retractable ceiling fan light, which includes a remote control. With transparent blades that retract out of sight when not in use and three SceneSwitch light settings, this light creates the perfect atmosphere in any space.

### Easy to experience

- Retractable ceiling fan with transparent blades
- Easy to install, safe to use
- Powerful, reliable performance
- Get year-round use
- Enjoy a comfortable breeze
- Convenient timers

### Ambient light effect

- Bright yet comfortable ceiling light

### Premium quality

- Quiet motor

# Highlights

## Retractable ceiling fan with transparent blades

Say goodbye to spinning shadows on the ceiling: this fan has transparent blades that can be folded into the light and out of sight when not in use.

## Easy to install, safe to use

The Philips LED retractable ceiling fan light has passed strict safety testing and includes drop-resistant screws and a sturdy design alongside other important safety features.

## Powerful, reliable performance

The Philips LED retractable ceiling fan light was designed to ensure powerful air circulation and continued reliability over time. Use it alone or with air conditioning for faster cooling.

## Get year-round use

With operation modes for both summer and winter, you'll get the best settings to circulate the air in your space all year round.

## Enjoy a comfortable breeze

Bring an island breeze to any room of your house with the Natural Breeze function, which offers dynamic speed settings for the fan.

## Convenient timers

Choose from two different timers that turn off your light after a certain amount of time — and set them with the remote control.

## Bright yet comfortable ceiling light

The Philips LED retractable ceiling fan light offers powerfully bright — yet comfortable — light for your home, which you can control with the included remote control or a wall switch.

## Quiet motor

The Philips LED retractable ceiling fan light offers a quiet motor, circulating the air in the room without any loud noises.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Round

## Design and finishing

- Color: white
- Material: metal/plastic

## Durability

- Average life (at 2.7 hrs/day): 15 year(s)
- Lumen maintenance factor: 70%
- Number of switch cycles: 15,000

## Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: Yes
- Centerpiece: Yes

## Light characteristics

- Color consistency: 6SDCM
- Color rendering index (CRI): 80
- Warm-up time to 60% light: <2

## Miscellaneous

- Especially designed for: Functional

## Other characteristics

- Lamp current: 290 mA
- Efficacy: 128 lm/W

## Power consumption

- Power factor: 0.9

## Product dimensions and weight

- Net weight: 7.2 kg
- Height: 41.8 cm
- Length: 51 cm
- Width: 51 cm

## Service

- Warranty: 2 year(s)

### Technical specifications

- Lifetime up to: 15,000 hour(s)
- Diameter: 510 mm
- Total lumen output fixture: 4500
- Light color: 2700/5500/4000
- Mains power: 220-240
- LED: Yes
- Built in LED: Yes
- Wattage bulb included: 28+35
- IP code: IP20
- Class of protection: Class I



Issue date: 2023-11-08  
Version: 0.291

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)