

PHILIPS

Downlight

Functional

DL029B

White

Dim



8719514443679



Control your light Experience with ease

Light up your space with Philips EyeComfort LED Downlight that provides a comfortable light source and ease to your eyes.

Light effect

- Bright light with uniform distribution

Control

- Dimmable

Durability

- Long life span up to 20,000 hours

Highlights

Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Dimmable

Allows you to change the mood by reducing LED brightness levels, from bright white light, to a cozy glow – just like traditional lamps.

Long life span up to 20,000 hours

Philips LED technology extends your product's lifetime up to 20,000 hours.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: White
- Material: Metal, Plastic

Durability

- Number of switch cycles: 15,000

Extra feature/accessory incl.

- Adjustable spot head: No
- Dimmable with remote control: No
- LED integrated: Yes
- Remote control included: No

Light characteristics

- Beam angle: 100 degree(s)
- Color consistency: 6 SDCM
- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office
- Style: Contemporary
- Type: Recessed Lights
- EyeComfort: Yes

Other characteristics

- Lamp current: 38 mA
- Efficacy: 106 lm/W

Product dimensions and weight

- Net weight: 0.23 kg
- Cut out length: 9.0 cm
- Cut out width: 9.0 cm
- Height: 5.6 cm
- Length: 11.4 cm
- Recessed distance: 0 cm
- Width: 11.4 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Lifetime up to: 30,000 h
- Diameter: 114 mm
- Total lumen output fixture: 800
- Light color: 3000/4000/6500
- Mains power: AC 220-240
- Fixture dimmable: Yes
- LED: Yes
- Wattage bulb included: 7.5
- IP code: IP40
- Class of protection: Class II

Packaging dimensions & weight

- EAN/UPC – product: 8719514443679
- Net weight: 1.84 kg
- Gross weight: 2.04 kg
- Height: 24.8 cm
- Length: 13.6 cm
- Width: 24.8 cm
- Material number (12NC): 929002531279



Issue date: 2024-02-02
Version: 0.77

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com