



Robust LED downlight which lasts for years

Philips LED Slim Downlight delivers a natural light effect for use in general lighting applications. It is a slim masterpiece for low ceilings, creating an elegant ambiance anywhere at home.

Comfortable light that's easy on your eyes.

Easy to experience

• Ideal for rooms with low ceilings, makes for an unobtrusive and subtle fixture.

Light effect

· Bright light with uniform distribution

Durability

• Long life span up to 15,000 hours

Highlights

Suitable for low ceilings Slim design Bright light with uniform distribution

To really light up your rooms, choose this uniform distribution light which throws light evenly across the space.

Long life span up to 15,000 hours

Philips LED technology extends your product's lifetime up to 15,000 hours.

Specifications

Bulb characteristics

Intended use: IndoorLamp shape: Round

Design and finishing

Color: WhiteMaterial: Plastic

Durability

• Average life (at 2.7 hrs/day): 15 year(s)

Lumen maintenance factor: 70%Number of switch cycles: 15,000

Extra feature/accessory incl.

· Adjustable spot head: No

• Dimmable with remote control: No

· LED integrated: Yes

· Remote control included: No

Light characteristics

Beam angle: 110 degree(s)Color consistency: 6 SDCM

· Color rendering index (CRI): 80

• Warm-up time to 60% light: <2

Miscellaneous

 Especially designed for: Bedroom, Living Room, Dining Room, Kitchen, Home Office

Style: Contemporary

Type: Recessed Lights

• EyeComfort: Yes

Other characteristics

Lamp current: 100 mAEfficacy: 80 lm/W

Power consumption

• Power factor: 0.5

Product dimensions and weight

Net weight: 0.24 kgCut out length: 15.0 cm

• Cut out tength: 15.0 cm

Height: 1.8 cmLength: 17 cm

· Recessed distance: 4.8 cm

• Width: 17 cm

Service

• Warranty: 1 year(s)

Technical specifications

· Lifetime up to: 15,000 hour(s)

• Diameter: 170 mm

· Total lumen output fixture: 960

· Light color: 6500

· Mains power: AC 220-240

· Fixture dimmable: No

• LED: Yes

Wattage bulb included: 12

• IP code: IP20

· Class of protection: Class II

Packaging dimensions and weight

• EAN/UPC - product: 8720169174283

Net weight: 0.24 kgGross weight: 0.42 kg

• Height: 21 cm

Length: 2.5 cmWidth: 17.5 cm

• Material number (12NC):

929003284601



Version: 0.119

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not Issue date: 2024-02-02

intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips