PHILIPS

3 Pin socket

Switches & Sockets

Smart Antibacterial

White

2 Module

25A

913713822701



Ensure a safer living with Smart Anti-bacterial Range

Philips Antibacterial Range kills 99% germs with in-built Silver Ion Technology.

Easy to use
- Shrouded terminals with captive screws
- Front insertion & front removal
- Glossy finish
- Low insert height
- Dual shutter technology
- Convenient grip for plug

Safe to use
- FR Grade Polycarbonate Material
- Safe to use even with wet hands

Longer lifetime
- Brass terminals
- Brass screw

Advanced
- Silver Ion Technology
- BactiSafe
- Non Toxic life long

Safe for kids
- Dual shutter technology

Choose for a sustainable solution
- RoHS compliant

Highlights

Shrouded terminals with captive screws
Shrouded terminals for easy installation. Screws wont come out during wire fixing.

Front insertion & front removal
Smart way to preserve your designer walls, remove your switch/socket without dismantle the plates. Inserts can be fixed or removed from front.

Glossy finish
Glossy external finish for easy to clean and long lasting finish.

Low insert height
Low insert height so that you get more space for wiring inside the installed box.

Dual shutter technology
Even 2 Pin Plug can be inserted easily without the help of any screw driver/ pencil to hold the top shutter.

Convenient grip for plug
Convenient gripping inside the socket for the inserted plug for better connectivity.

FR Grade Polycarbonate Material
Best quality polycarbonate material which doesn't catch fire easily, Material also clears the Glow Wire Test @ 850 Degree Celsius.

Safe to use even with wet hands
No seepage of water due to precision & covered design.

Brass terminals
Brass terminal for connection for longer, uninterrupted life.

Brass screw
Brass screw for longer, carefree operations.

Silver Ion Technology
Material has Silver Ions which turn bacteria into deadly zombies.

BactiSafe
Kills 99% bacteria as per test protocol JIS Z 2801:2010 conducted on E. Coli & Staphylococcus.

Non Toxic life long
Silver Ion technology has longer life of more than 10 years as it's in built in material & has no side effects.

Dual shutter technology
Separate in built shutter for L/N pin & earth pin make easy fitment even for 2 pin plug, also makes it safer even when kids are around. Separate shutter prevents from accidental finger insertion.

RoHS compliant
All the switches/sockets are free from any hazardous substance to the environment making it safe to use.

Specifications

Design and finishing
- Color: White
- Material: PC
- Module/Gang: 2 Module
- Socket/connector Type: Combination Socket
- Product Range: Smart Antibacterial
- Minimum Installation Box Depth: 50 mm

Durability
- Number of Operation Cycles: 5,000

Interactivity
- Current (A): 25A

Other characteristics
- Installation Type: Fast Installation
- Indicator Type: No Indicator

Power
- Electrical Load Type: Resistive load

Power consumption
- Voltage: 240 V

Product dimensions & weight
- Length: 5 cm
- Width: 4.5 cm
- Depth: 4.5 cm

Service
- Warranty: 2 year(s)

Technical specifications
- Frequency: 50 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718699738228
- Net weight: 0.040 kg
- Gross weight: 0.041 kg
- Height: 4.500 cm
- Length: 5.000 cm
- Width: 4.500 cm
- Material number (12NC): 913713822701

Issue date: 2023-11-08
Version: 0.269

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com