

# PHILIPS

## Trip starter

Switches & Sockets

Smart Antibacterial

White

25A

913713824501



## Ensure a safer living with Smart Anti-bacterial Range

Philips Antibacterial Range kills 99% germs with in-built Silver Ion Technology.

### Easy to use

- Gloss finish

### Safe to use

- FR grade material

### Longer lifetime

- Plastic for outer body with brass terminals
- Sustain high heat

### Advanced

- Silver Ion Technology
- BactiSafe
- Non Toxic life long

### Durability

- Air vents

# Highlights

## Gloss finish

Glossy white finish which flushes with the wall and also easy to clean.

## FR grade material

FR Grade material is used while making the circuit breaker so that it detracts accidental fires.

## Plastic for outer body with brass terminals

Plastic for outer body with brass terminals.

## Sustain high heat

PBT material used as base material to withstand high heat.

## Silver Ion Technology

Material has Silver Ions which turn bacteria into deadly zombies.

## BactiSafe

Kills 99% bacteria as per test protocol JIS Z 2801:2010 conducted on E. Coli & Staphylococcus.

## Non Toxic life long

Silver Ion technology has longer life of more than 10 years as it's in built in material & has no side effects.

## Air vents

Designed with Air vents for better air circulation which helps in keeping the product cools and improves the life.

# Specifications

## Design and finishing

- Color: White
- Material: metal/plastic
- Module/Gang: 1 Module
- Product Range: Smart Antibacterial
- Minimum Installation Box Depth: 5 cm

## Durability

- Number of Operation Cycles: 4,000

## Interactivity

- Current (A): 25

## Other characteristics

- Installation Type: Fast Installation
- Indicator Type: No Indicator

## Power consumption

- Voltage: 240 V

## Product dimensions & weight

- Length: 5 cm
- Width: 2.25 cm
- Depth: 5.1 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Frequency: 50 Hz

## Packaging dimensions and weight

- EAN/UPC - product: 8718699738761
- Net weight: 0.058 kg
- Gross weight: 0.059 kg
- Height: 5.100 cm
- Length: 5.000 cm
- Width: 2.250 cm
- Material number (12NC): 913713824501



Issue date: 2022-07-26  
Version: 0.24

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)