

# PHILIPS

Electronic Foot  
Lamp

Switches & Sockets

Smart Antibacterial

White

2 Module

913713825201



## Ensure a safer living with Smart Anti- bacterial Range

Philips Antibacterial Range kills 99% germs with in-built Silver Ion Technology.

### Easy to use

- Front insertion & front removal

### Safe to use

- FR Grade Polycarbonate Material

### Advanced

- Silver Ion Technology
- BactiSafe
- Non Toxic life long

### Choose for a sustainable solution

- RoHS compliant

### Convenience

- Use as foot lamp

# Highlights

## Front insertion & front removal

Smart way to preserve your designer walls, remove your switch/socket without dismantle the plates. Inserts can be fixed or removed from front.

## FR Grade Polycarbonate Material

Best quality polycarbonate material which doesn't catch fire easily, Material also clears the Glow Wire Test @ 850 Degree Celsius.

## Silver Ion Technology

Material has Silver Ions which turn bacteria into deadly zombies.

## BactiSafe

Kills 99% bacteria as per test protocol JIS Z 2801:2010 conducted on E. Coli & Staphylococcus.

## Non Toxic life long

Silver Ion technology has longer life of more than 10 years as it's in built in material & has no side effects.

## RoHS compliant

All the switches/sockets are free from any hazardous substance to the environment making it safe to use.

## Use as foot lamp

Soft light which can be used as night lamp or step light in stairs etc.

# Specifications

## Design and finishing

- Color: White
- Material: metal/plastic
- Module/Gang: 2 Module
- Product Range: Smart Antibacterial
- Minimum Installation Box Depth: 5 cm

## Other characteristics

- Installation Type: Fast Installation
- Indicator Type: LED

## Power consumption

- Voltage: 240 V

## Product dimensions & weight

- Length: 5 cm
- Width: 4.5 cm
- Depth: 6.4 cm

## Service

- Warranty: 2 year(s)

## Technical specifications

- Frequency: 50 Hz

## Packaging dimensions and weight

- EAN/UPC - product: 8718699738976
- Net weight: 0.003 kg
- Gross weight: 0.003 kg
- Height: 5.380 cm
- Length: 5.000 cm
- Width: 4.500 cm
- Material number (12NC): 913713825201



Issue date: 2023-11-08  
Version: 0.265

© 2023 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)