

PHILIPS

2.1 A USB Charger

Switches & Sockets

Smart Antibacterial

White

1 Module

913713825301



Ensure a safer living with Smart Anti- bacterial Range

Philips Antibacterial Range kills 99% germs with in-built Silver Ion Technology.

Easy to use

- Front insertion & front removal
- Glossy finish
- Indicator to display on/off

Safe to use

- FR Grade Polycarbonate Material

Advanced

- Silver Ion Technology
- BactiSafe
- Non Toxic life long

Choose for a sustainable solution

- RoHS compliant

Convenience

- USB charging 2.0A

Highlights

Front insertion & front removal

Smart way to preserve your designer walls, remove your switch/socket without dismantle the plates. Inserts can be fixed or removed from front.

Glossy finish

Glossy external finish for easy to clean and long lasting finish.

Indicator to display on/off

Red marking provided on the top for 16A & above rated switch for convenience during installation.

FR Grade Polycarbonate Material

Best quality polycarbonate material which doesn't catch fire easily, Material also clears the Glow Wire Test @ 850 Degree Celsius.

Silver Ion Technology

Material has Silver Ions which turn bacteria into deadly zombies.

BactiSafe

Kills 99% bacteria as per test protocol JIS Z 2801:2010 conducted on E. Coli & Staphylococcus.

Non Toxic life long

Silver Ion technology has longer life of more than 10 years as it's in built in material & has no side effects.

RoHS compliant

All the switches/sockets are free from any hazardous substance to the environment making it safe to use.

USB charging 2.0A

Suitable for iPad, iPhone & Android Phone. Fast charging due to 2A power output.

Specifications

Design and finishing

- Color: White
- Material: metal/plastic
- Module/Gang: 1 Module
- Minimum Installation Box Depth: 50 mm

Interactivity

- Current (A): 2

Other characteristics

- Installation Type: Fast Installation
- Indicator Type: LED

Power consumption

- Voltage: 240 V

Product dimensions & weight

- Length: 5 cm
- Width: 2.25 cm
- Depth: 6.4 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Frequency: 50 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718699739003
- Net weight: 0.035 kg
- Gross weight: 0.036 kg
- Height: 5.300 cm
- Length: 5.000 cm
- Width: 2.250 cm
- Material number (12NC): 913713825301



Issue date: 2021-08-31
Version: 0.259

© 2021 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com