

PHILIPS

2 Pole Isolator

Circuit Breakers

100A

913713935349



SafeTechnology that protects your home

Philips Isolators range with SafeTechnology, adds extra protection & safety to your home.

Easy to use

- Snap locks
- Gloss finish

Safe to use

- FR grade material

Pure and elegant design

- Compact design

Durability

- Air circulation
- Brass Connectors
- Copper contact
- Double break capacity

Convenience

- Description window

Highlights

Snap locks

Plastic body fitted with snap lock this helps in easy to lock and unblock.

Gloss finish

Glossy white finish which flushes with the wall and also easy to clean.

FR grade material

FR Grade material is used while making the circuit breaker so that it detracts accidental fires.

Compact design

Convenient to fit in Distribution box along with MCB.

Air circulation

Designed with Air channels which provide better air circulation around individual poles. This improves the thermal situation and thus improves the life of the product.

Brass Connectors

Brass connectors for Phase and Neutral. This gives longer life to the product.

Copper contact

Copper contact which ensure better continuity.

Double break capacity

Ensure Longer Life.

Description window

Description window with label to identify the connection, Convenience to use during installation and maintenance.

Specifications

Design and finishing

- Color: Grey
- Material: Metal, Plastic
- Minimum Installation Box Depth: 10 cm
- Connection Terminals: Saddle

Interactivity

- Current (A): 100

Miscellaneous

- Approval Marks: BIS Certificate

Other characteristics

- Installation Type: Din Rail

Power

- Electrical Load Type: Inductive load

Power consumption

- Voltage: 240 V

Product dimensions and weight

- Length: 9.2 cm
- Width: 7.344 cm
- Depth: 3.56 cm

Service

- Warranty: 1 year(s)

Technical specifications

- Frequency: 50 Hz
- Number of Poles: 2 Pole

Packaging dimensions and weight

- EAN/UPC – product: 8718696502846
- Net weight: 210.74 g
- Gross weight: 221.15 g
- Height: 3.6 cm
- Length: 9.2 cm
- Width: 7.3 cm
- Material number (12NC): 913713935349



Issue date: 2024-02-02
Version: 0.268

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com