

PHILIPS

USB Charger

Switches & Sockets

Durro

White

1 Module

913713991001



Durability with style

Enhance your home décor with smooth, curved & highly durable switches & accessories, from Philips Durro range.

Easy to use

- Front insertion & front removal
- Glossy finish
- Indicator to display on/off

Safe to use

- FR Grade Polycarbonate Material

Choose for a sustainable solution

- RoHS compliant

Convenience

- USB charging 2.0A

Highlights

Front insertion & front removal

Smart way to preserve your designer walls, remove your switch/socket without dismantle the plates. Inserts can be fixed or removed from front.

Glossy finish

Glossy external finish for easy to clean and long lasting finish.

Indicator to display on/off

Red marking provided on the top for 16A & above rated switch for convenience during installation.

FR Grade Polycarbonate Material

Best quality polycarbonate material which doesn't catch fire easily, Material also clears the Glow Wire Test @ 850 Degree Celsius.

RoHS compliant

All the switches/sockets are free from any hazardous substance to the environment making it safe to use.

USB charging 2.0A

Suitable for iPad, iPhone & Android Phone. Fast charging due to 2A power output.

Specifications

Design and finishing

- Color: White
- Material: Metal, Plastic
- Module/Gang: 1 Module
- Product Range: Durro
- Minimum Installation Box Depth: 5 cm

Durability

- Number of Operation Cycles: 5,000

Interactivity

- Current (A): 2

Other characteristics

- Installation Type: Screwed Installation
- Indicator Type: LED

Power

- Electrical Load Type: Resistive load

Power consumption

- Voltage: 240 V

Product dimensions and weight

- Length: 5.5 cm
- Width: 2.4 cm
- Depth: 4.7 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Frequency: 50 Hz

Packaging dimensions and weight

- EAN/UPC - product: 8718699685096
- Net weight: 0.04 kg
- Gross weight: 0.04 kg
- Height: 4.7 cm
- Length: 5.5 cm
- Width: 2.4 cm
- Material number (12NC): 913713991001



Issue date: 2024-02-02
Version: 0.278

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com