

PHILIPS

Trip starter

Switches & Sockets

Durro

White

32A

913713993001



Durability with style

Enhance your home décor with smooth, curved & highly durable switches & accessories, from Philips Durro range.

Easy to use

- Gloss finish

Safe to use

- FR grade material

Longer lifetime

- Plastic for outer body with brass terminals
- Sustain high heat

Durability

- Air vents

Highlights

Gloss finish

Glossy white finish which flushes with the wall and also easy to clean.

FR grade material

FR Grade material is used while making the circuit breaker so that it detracts accidental fires.

Plastic for outer body with brass terminals

Plastic for outer body with brass terminals.

Air vents

Designed with Air vents for better air circulation which helps in keeping the product cool and improves the life.

Sustain high heat

PBT material used as base material to withstand high heat.

Specifications

Design and finishing

- Color: White
- Material: metal/plastic
- Module/Gang: 1 Module
- Product Range: Durro
- Minimum Installation Box Depth: 5 cm

Durability

- Number of Operation Cycles: 4,000

Interactivity

- Current (A): 32

Other characteristics

- Installation Type: Fast Installation
- Indicator Type: No Indicator

Power consumption

- Voltage: 240 V

Product dimensions & weight

- Length: 5.5 cm
- Width: 2.4 cm
- Depth: 5.1 cm

Service

- Warranty: 2 year(s)

Technical specifications

- Frequency: 50 Hz

Design and finishing

- Color: White
- Number of Operation Cycles: 4,000
- EAN/UPC - product: 8718699685782
- Warranty: 2 year(s)
- Current (A): 32
- Net weight: 0.055 kg
- Material: metal/plastic
- Gross weight: 0.056 kg
- Module/Gang: 1 Module
- Height: 5.500 cm
- Installation Type: Fast Installation
- Length: 5.500 cm
- Product Range: Durro
- Indicator Type: No Indicator
- Width: 2.400 cm
- Voltage: 240 V
- Minimum Installation Box Depth: 5 cm
- Material number (12NC): 913713993001
- Length: 5.5 cm
- Width: 2.4 cm
- Frequency: 50 Hz
- Depth: 5.1 cm



Issue date: 2022-06-12
Version: 0.265

© 2022 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com