



#	COMPONENT	QTY
1	DIFFUSER	1
2	SCREW	2
3	CONTROL GEAR - SENSOR	1
4	SCREW	2
5	INNER DIFFUSER	1
6	SCREW	1
7	LIGHT SOURCE - LED MODULE	1
8	TERMINAL BLOCK	1
9	BASE	1

SKU	Color	Country
915004988901	STAINLESS STEEL	EU

Warnings

Always make sure the luminaire is detached from the mains socket
 Always make sure the DC cable is detached from the power supply
 Staring at the operating light source may cause eye injury

#	Disassemble/dismantle steps	Tools needed
a	REMOVE DIFFUSER (1) BY UNSCREWING THE SCREWS (2)	CROSS HEAD SCREW DRIVER
b	SEPARATE THE CONNECTOR OF LIGHT SOURCE - LED MODULE (7) AND CONTROL GEAR - SENSOR (3)	-
c	UNSNAP AND REMOVE THE INNER DIFFUSER (5)	FLAT HEAD SCREW DRIVER
d	REMOVE WIRES OF LIGHT SOURCE - LED MODULE (7) FROM TERMINAL BLOCK (8) BY UNSCREWING THE TERMINAL BLOCK (8)	FLAT HEAD SCREW DRIVER
e	REMOVE LIGHT SOURCE - LED MODULE (7) FROM BASE (9) BY UNSCREWING THE SCREW (6)	CROSS HEAD SCREW DRIVER
f	REMOVE CONTROL GEAR - SENSOR (3) FROM DIFFUSER (1) BY UNSCREWING THE SCREWS (4)	CROSS HEAD SCREW DRIVER
g	REPLACE NEW CONTROL GEAR - SENSOR (3) TO DIFFUSER (1) BY SCREWING THE SCREW (4)	CROSS HEAD SCREW DRIVER
h	REPLACE NEW LIGHT SOURCE - LED MODULE (7) TO BASE (9) BY SCREWING THE SCREW (6)	CROSS HEAD SCREW DRIVER
i	SCREW WIRES OF LIGHT SOURCE - LED MODULE (7) TO TERMINAL BLOCK (8)	FLAT HEAD SCREW DRIVER
j	SNAP BACK INNER DIFFUSER (5) TO BASE (9)	-
k	CONNECT LIGHT SOURCE - LED MODULE (7) AND CONTROL GEAR - SENSOR (3)	-
l	FIX DIFFUSER (1) BY SCREWING THE SCREWS (2)	CROSS HEAD SCREW DRIVER

STATUS	DESCRIPTION	DESIGN ID	
2024-01-24	Calgary wall lantern inox 1x3W 230V	DOC 12NC	
NAME WH	LOCAL PART ID	SH. 1	SH.
CHECKED	DATE		A3-P