



SKU	Color	Country
915005193902	DARK GREY	EU
915005193901	DARK GREY	EU

#	COMPONENT	QTY
1	COVER	1
2	DIFFUSER	1
3	SCREW	1
4	INNER DIFFUSER	1
5	LIGHT SOURCE - LED MODULE	1
6	SCREW	1
7	CONTROL GEAR - PSU	1
8	BASE	1
9	SCREW	2
10	CLAMPER	1
11	SCREW	1
12	TERMINAL BLOCK	1
13	SCREW	2
14	CLOSED END CONNECTOR	1
15	CONTROL GEAR - SENSOR	1
16	SCREW	2

Warnings

Always make sure the luminaire is detached from the mains socket
 Always make sure the DC cable is detached from the power supply
 Staring at the operating light source may cause eye injury

#	Disassemble/dismantle steps	Tools needed
a	REMOVE COVER (1) AND DIFFUSER (2) BY UNSCREWING THE SCREWS (13)	CROSS HEAD SCREW DRIVER
b	REMOVE CLAMPER (10) BY UNSCREWING THE SCREWS (9)	CROSS HEAD SCREW DRIVER
c	REMOVE TERMINAL BLOCK (12) BY UNSCREWING THE SCREW (10)	CROSS HEAD SCREW DRIVER
d	REMOVE WIRE OF THE CONTROL GEAR - PSU (7) AND WIRES OF THE CONTROL GEAR - SENSOR (14) FROM THE TERMINAL BLOCK (12) BY UNSCREWING THE TERMINAL BLOCK (12)	FLAT HEAD SCREW DRIVER
e	REMOVE THE CLOSED END CONNECTOR (14)	PINCER
f	REMOVE INNER DIFFUSER (4) BY UNSCREWING THE SCREW (3)	CROSS HEAD SCREW DRIVER
g	REMOVE WIRES OF THE CONTROL GEAR - PSU (7) FROM THE LIGHT SOURCE - LED MODULE (5)	SOLDER IRON
h	REMOVE THE CONTROL GEAR - PSU (7) FROM THE BASE BY UNSCREWING THE SCREWS (6)	CROSS HEAD SCREW DRIVER
i	REMOVE THE CONTROL GEAR - SENSOR (15) FROM THE BASE BY UNSCREWING THE SCREWS (16)	CROSS HEAD SCREW DRIVER

STATUS	DESCRIPTION	DESIGN ID
2021-04-12	Arbour IR 4000K wall lantern anthracite Arbour IR wall lantern anthracite 1x6W	DOC 12NC
NAME WH	LOCAL PART ID	SH. 1
CHECKED	DATE	SH. A3-P