

PHILIPS

Bathroom Wall Light

myBathroom

20W; Warm White; 2000 lumen; In-built LED;

IP44 rating ensures protection from dust and moisture;

Bright light output at 100 lumen/watt;

Elegant design

919215851238



Perfect for bathroom as it offers bright light output

The word 'Meraki' refers to the soul, creativity, or love put into creating something! These wall lights embody the exact meaning of this word, as they have been crafted with utmost precision, so that you can get the best out of your 'me' time which is spent in front of the mirror. With a bright light output and protection from moisture and water splashes, Meraki wall lights are a perfect accessory for bathrooms and powder rooms. Due to their sleekness, they can also be used in balconies, lobbies or staircase very easily.

Light modes

- Light up your home with extra brightness

Highlights

Extra brightness

Brighten up your home with this high lumen light bulb. With sufficient

brightness to help you engage in your tasks, or for relaxing activities, this light

also works very well in large spaces with high ceilings.

Specifications

Bulb characteristics

- Intended use: Indoor

Design and finishing

- Color: Chrome
- Material: Chrome-plated MS with PC diffuser

Extra feature/accessory incl.

- Adjustable height: No
- Adjustable spot head: No
- Anti rust anti dust: No
- Clamp included: Yes
- LED integrated: Yes
- Perfectly suited for ambiance creation: Yes
- Perfectly suited for horizontal/vertical mounting: Yes
- Premium quality material: Yes
- Warm White Light: Yes

Light characteristics

- Color rendering index (CRI): 80

Miscellaneous

- Especially designed for: Bathroom
- Style: Functional

Product dimensions and weight

- Net weight: 0.529 kg
- Height: 13 cm
- Length: 60 cm
- Width: 6.5 cm
- Height: 5.12 inch
- Length: 23.62 inch
- Width: 2.56 inch

Service

- Warranty: 1 year(s)

Technical specifications

- Total lumen output fixture: 2000
- Bulb technology: LED
- Light color: warm white
- Mains power: 220-240 V
- LED: Yes
- Built in LED: Yes
- Energy class included light source: Built in LED
- IP code: IP44
- Light source replaceable: No

Packaging dimensions and weight

- EAN/UPC – product: 8720169275614
- Net weight: 0.53 kg
- Gross weight: 0.75 kg
- Height: 14 cm
- Length: 61 cm
- Width: 7 cm
- Material number (12NC): 919215851238



Issue date: 2024-02-02
Version: 0.194

© 2024 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com