



Actinic BL PL-S/PL-L

PL-L 36W/10/4P 1CT/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	2G11
Life to 50% Failures (Nom)	11,000 hour(s)
Useful Life (Nom)	5,000 hour(s)
Light Technical	
Color Code	210 [leadfree 360 glass (10)]
Chromaticity Coordinate X (Nom)	220
Chromaticity Coordinate Y (Nom)	215
UV Depreciation at 2000 h	15 %
UV Depreciation at 5000 h	50 %


Operating and Electrical	
Power Consumption	36 W
Lamp Current (Nom)	0.435 A
Voltage (Nom)	106 V
Mechanical and Housing	
Bulb Shape	2xT16
Net Weight (Piece)	0.229 lb
Approval and Application	
Mercury (Hg) Content (Max)	2.1 mg

Actinic BL PL-S/PL-L

Mercury (Hg) Content (Nom)	2.0 mg
UV	
UV-A Radiation 100Hr (IEC)	8.5 W
Product Data	
Order product name	Insect PL-L 36W /10
Full product name	PL-L 36W/10/4P 1CT/25
Full product code	871150026481740


Order code	232934
Material Nr. (12NC)	927903421007
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500264817
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500264824

Dimensional drawing



Product	D1 (max)	D (max)	C1	A (max)	B (max)	C (max)
Insect PL-L 36W /10	3/4 inch	1-9/16 inch	13/16 inch	15-1/8 inch	16-3/16 inch	16-7/16 inch

Photometric data



Spectral Power Distribution Colour - Insect PL-L 36W /10

