



MASTER PL-L 4 Pin

36 W 4 Pin Cool daylight Non integrated compact fluorescent

Energy-saving compact fluorescent lamps. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 2 parallel fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Luminous Efficacy (rated) (Nom)	
Cap-Base	2G11		80 lm/W
Nominal lifetime	15,000 hour(s)	Color rendering index (CRI)	80
Life to 50% Failures (Nom)	15,000 hour(s)		
Light Technical		Operating and Electrical	
Color Code	865 [CCT of 6500K]	Power Consumption	36 W
Luminous Flux	2,900 lm	Lamp Current (Nom)	0.435 A
Color Designation	Cool Daylight		
Correlated Color Temperature (Nom)	6500 K	Controls and Dimming	
		Dimmable	Yes

MASTER PL-L 4 Pin

Mechanical and Housing

Net Weight (Piece) 104.000 g

Approval and Application

Mercury (Hg) Content (Nom) 2.0 mg

Energy Consumption kWh/1000 h 40 kWh

Product Data

Order product name 36 W 4 Pin Cool daylight Non integrated compact fluorescent

Full product name 36 W 4 Pin Cool daylight Non integrated compact fluorescent

Full product code 871150063520441

Order code 927903486572

Material Nr. (12NC) 927903486572


Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 8711500635204

Numerator - Packs per outer box 25


EAN/UPC - Case 8711500635211

Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
36 W 4 Pin Cool daylight Non integrated compact fluorescent	39.0 mm	18.0 mm	384.2 mm	410 mm	416.6 mm

Photometric data



Spectral Power Distribution Colour - MASTER PL-L 36W/865/4P 1CT/25

MASTER PL-L 4 Pin

