



Actinic BL PL-L Secura

PL-L 36W/10/4P Secura 1CT/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL PL-L Secura lamps are perfect for attracting insects. With the compact PL-L product format in a variety of wattages, new attractive designs are possible. Furthermore, these lamps have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	2G11
Life to 50% Failures (Nom)	10,000 hour(s)
Light Technical	
Color Code	10
Chromaticity Coordinate X (Nom)	228
Chromaticity Coordinate Y (Nom)	215


UV Depreciation at 2000 h	20 %
UV Depreciation at 5000 h	40 %
Operating and Electrical	
Power Consumption	36 W
Lamp Current (Nom)	0.440 A
Voltage (Nom)	108 V

Actinic BL PL-L Secura

Mechanical and Housing	
Bulb Shape	2xT16
Net Weight (Piece)	0.293 lb
Approval and Application	
Mercury (Hg) Content (Max)	2.0 mg
Mercury (Hg) Content (Nom)	2
UV	
UV-A Radiation 100Hr (IEC)	7.7 W
Product Data	
Order product name	PL-L 36W/10/4P SECURA 1CT/25


Full product name	PL-L 36W/10/4P Secura 1CT/25
Full product code	871829119443900
Order code	285049
Material Nr. (12NC)	927909121001
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291194439
Numerator - Packs per outer box	25
EAN/UPC - Case	8718291194446

Dimensional drawing



Product	D1 (max)	D (max)	C1	A (max)	B (max)	C (max)
PL-L 36W/ 10/4P SECURA 1CT/25	1-1/16 inch	1-5/8 inch	13/16 inch	15-15/16 inch	16-15/16 inch	17-3/16 inch

Photometric data



Spectral Power Distribution Colour - PL-L 36W/10/4P SECURA 1CT/25

Actinic BL PL-L Secura

