



# PL-T Triple 4-Pin Base

## PL-T 57W/841/A/4P 1CT/5X10BOX ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

### Product data

| General Information |         |
|---------------------|---------|
| Cap-Base            | GX24q-5 |

| Light Technical                    |                    |
|------------------------------------|--------------------|
| Color Code                         | 841 [CCT of 4100K] |
| Luminous Flux                      | 4,300 lm           |
| Color Designation                  | Cool White (CW)    |
| Correlated Color Temperature (Nom) | 4100 K             |
| Luminous Efficacy (Rated) (Min)    | 76 lm/W            |
| Color rendering index (CRI)        | 82                 |

| Operating and Electrical |         |
|--------------------------|---------|
| Power Consumption        | 51.0 W  |
| Lamp Current (Nom)       | 0.320 A |

| Controls and Dimming |     |
|----------------------|-----|
| Dimmable             | Yes |

| Mechanical and Housing |           |
|------------------------|-----------|
| Net Weight (Piece)     | 101.000 g |


| Approval and Application   |        |
|----------------------------|--------|
| Mercury (Hg) Content (Nom) | 1.4 mg |

| Product Data                    |                                    |
|---------------------------------|------------------------------------|
| Order product name              | PL-T 57W/841/A/4P 1CT/5X10BOX ALTO |
| Full product name               | PL-T 57W/841/A/4P 1CT/5X10BOX ALTO |
| Order code                      | 146332                             |
| Material Nr. (12NC)             | 927914084020                       |
| Numerator - Quantity Per Pack   | 1                                  |
| EAN/UPC - Product/Case          | 046677146337                       |
| Numerator - Packs per outer box | 10                                 |
| EAN/UPC - Case                  | 50046677146332                     |



# PL-T Triple 4-Pin Base

## Dimensional drawing




| Product                            | D (max) | A (max)  | B (max)  | C (max)  |
|------------------------------------|---------|----------|----------|----------|
| PL-T 57W/841/A/4P 1CT/5X10BOX ALTO | 41 mm   | 157.7 mm | 182.0 mm | 197.7 mm |

## Lifetime



Lumen Maintenance Diagram - PL-T 57W/841/A/4P 1CT/5X10BOX ALTO

Life expectancy diagram - 3 hour cycle



Life expectancy diagram - 12 hour cycle

## PL-T Triple 4-Pin Base

