



Actinic BL TL-D(K) Secura

Actinic BL TL-D 18W/10 Secura 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL-D(K) Secura lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	13,000 hour(s)
Useful Life (Nom)	9,000 hour(s)
Light Technical	
Color Code	10
Color Designation	Actinic
Chromaticity Coordinate X (Nom)	220


Chromaticity Coordinate Y (Nom)	200
UV Depreciation at 2000 h	20 %
UV Depreciation at 5000 h	30 %
Operating and Electrical	
Power Consumption	18 W
Lamp Current (Nom)	0.36 A
Voltage (Nom)	59 V

Actinic BL TL-D(K) Secura

Mechanical and Housing	
Bulb Shape	T26
Net Weight (Piece)	0.281 lb
Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg
CE mark	Yes
UV	
UV-A Radiation 100Hr (IEC)	4.5 W
Product Data	
Order product name	Actinic BL TL-D 18W/10 Secura 1SL/25


Full product name	Actinic BL TL-D 18W/10 Secura 1SL/25
Full product code	872790085383400
Order code	258996
Material Nr. (12NC)	928048201003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900853834
Numerator - Packs per outer box	25
EAN/UPC - Case	8727900853841

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 18W/10 Secura 1SL/25	1-1/8 inch	23-1/4 inch	23-1/2 inch	23-7/16 inch	23-13/16 inch

Photometric data



Spectral Power Distribution Colour - Actinic BL TL-D 18W/10 Secura 1SL/25

Actinic BL TL-D(K) Secura

