



MASTER SON-T APIA Plus Xtra

MST SON-T APIA Plus Xtra 400W E40 1SL/12

High Pressure Sodium lamp with clear tubular outer bulb shape, high output and longest reliable lifetime

Warnings and Safety

- Control gear must include end-of-life protection (IEC60662, IEC 62035)

Product data

General Information	
Cap base	E40
Operating position	UNIVERSAL [Any or Universal (U)]
Flux measurement reference	Sphere
Life to 50% failures (nom.)	45,000 h

Light Technical	
Colour Code	- [Not Specified]
Luminous Flux	55,400 lm
Chromaticity Coordinate X (Nom)	0.535
Chromaticity Coordinate Y (Nom)	0.42
Correlated Colour Temperature (Nom)	2000 K
Luminous efficacy (rated) (nom.)	140 lm/W
Colour rendering index (CRI)	-
Arc Length O (Nom)	83 mm

Operating and Electrical	
Power Consumption	397.0 W
Voltage (nom.)	98 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T46
Net Weight (Piece)	0.175 kg

Approval and Application	
Energy Efficiency Class	E
Mercury (Hg) content (max.)	19.6 mg
Mercury (Hg) content (nom.)	19.6 mg
Energy consumption kWh/1,000 hours	397 kWh
EPREL Registration Number	473378
CE mark	Yes


Product Data	
Order product name	MST SON-T APIA Plus Xtra 400W E40 1SL/12
Full product name	MST SON-T APIA Plus Xtra 400W E40 1SL/12
Full EOC	872790092741200

MASTER SON-T APIA Plus Xtra

Order code	928150519227
Material no. (12 NC)	928150519227
Local order code	400SONTPLUSXTRA
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8727900927412




Numerator – packs per outer box	12
EAN/UPC – Case	8727900927429

Dimensional drawing



Product	D (max)	O	L	C (max)
MST SON-T APIA Plus Xtra 400W E40 1SL/12	48 mm	83 mm	175 mm	283 mm



Photometric data



Light Distribution Diagram - MST SON-T APIA Plus Xtra 400W E40 1SL/12

Spectral Power Distribution Colour - MST SON-T APIA Plus Xtra 400W E40 1SL/12

Lifetime



LDLE_SONTAPIA_0005-Life expectancy diagram

Lumen Maintenance Diagram - MST SON-T APIA Plus Xtra 400W E40 1SL/12

MASTER SON-T APIA Plus Xtra

