



MASTER SON-T PIA Plus



MST SON-T PIA Plus 50W/220 E27 1SL/12

High Pressure Sodium lamp with clear tubular outer bulb, high output and long reliable lifetime

Warnings and Safety

- Control gear must include end-of-life protection (IEC60662, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	E27
Operating position	UNIVERSAL [Any or Universal (U)]
Flux measurement reference	Sphere
Life to 50% failures (nom.)	30,000 h

Light Technical	
Colour Code	220 [CCT of 2000K]
Luminous Flux	4,500 lm
Chromaticity Coordinate X (Nom)	0.54
Chromaticity Coordinate Y (Nom)	0.42
Correlated Colour Temperature (Nom)	1900 K
Luminous efficacy (rated) (nom.)	83 lm/W
Colour rendering index (CRI)	-
Arc Length O (Nom)	35 mm

Operating and Electrical	
Power Consumption	54.5 W
Voltage (nom.)	91 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T35
Net Weight (Piece)	0.047 kg


Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	9.8 mg
Mercury (Hg) content (nom.)	9.8 mg
Energy consumption kWh/1,000 hours	55 kWh

MASTER SON-T PIA Plus

EPREL Registration Number	473390
CE mark	Yes
Product Data	
Order product name	MST SON-T PIA Plus 50W/220 E27 1SL/12
Full product name	MST SON-T PIA Plus 50W/220 E27 1SL/12
Full EOC	871150019265315
Order code	928151900028


Material no. (12 NC)	928151900028
Local order code	50SONTPLUS
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500192653
Numerator – packs per outer box	12
EAN/UPC - Case	8711500193094

Dimensional drawing




Product	D (max)	O	L	C (max)
MST SON-T PIA Plus 50W/220 E27 1SL/12	36 mm	35 mm	104 mm	156 mm

Photometric data





Light Distribution Diagram - MST SON-T PIA Plus 50W/220 E27 1SL/12



Spectral Power Distribution Colour - MST SON-T PIA Plus 50W/220 E27 1SL/12

MASTER SON-T PIA Plus

Lifetime



Lumen Maintenance Diagram - MST SON-T PIA Plus 50W/220 E27 1SL/12

LDLE_SON-TPIA_0007-Life expectancy diagram

