



MSR Platinum (Touring/Stage)

MSR Platinum 35 1CT/16

Today's stage designs call for lighting solutions which deliver high brightness and high-contrast beams to avoid shadow creation, as well as more compact luminaire and fixture designs to improve creative choice and design flexibility. Addressing this need, we have developed an incredibly powerful, brilliant and lightweight, compact system for the most amazing light experience – MSR Platinum 35. This lamp system provides a powerful and innovative tool to create intense lighting and delivers the same good light quality as other MSR lamps. The exceptionally short arc generates sparkling, bright light and this ultra-compact design makes the lamp suitable for smaller stage lighting fixtures.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information			
Cap-Base	PGJX36	Chromaticity Coordinate X (Nom)	0.295
Operating Position	UNIVERSAL [Any or Universal (U)]	Chromaticity Coordinate Y (Nom)	0.313
Life to 50% Failures (Nom)	1,000 hour(s)	Correlated Color Temperature (Nom)	8500 K
		Luminous Efficacy (rated) (Nom)	69 lm/W
		Color rendering index (CRI)	73
		Arc Length O (Nom)	3.0 mm
Light Technical			
Color Code	2		
Luminous Flux	53,300 lm		

MSR Platinum (Touring/Stage)

Operating and Electrical	
Power Consumption	773 W
Lamp Current (Nom)	12.0 A
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Net Weight (Piece)	0.117 lb
Approval and Application	
CE mark	Yes


Product Data	
Order product name	MSR Platinum 35 1CT
Full product name	MSR Platinum 35 1CT/16
Full product code	871829112006300
Order code	245977
Material Nr. (12NC)	928190905114
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291120063
Numerator - Packs per outer box	16
EAN/UPC - Case	8718291120070

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR Platinum 35 1CT	15/16 inch	1/8 inch	2-3/16 inch	2-1/4 inch	2-1/4 inch	4-9/16 inch

Photometric data



Spectral Power Distribution Colour - MSR Platinum 35 1CT

MSR Platinum (Touring/Stage)

