



# MASTERCcolour CDM-TC Elite



## MASTERC CDM-TC Elite 70W/942 G8.5 1CT

Single-ended, compact size, high-efficiency Ceramic Metal Halide discharge lamp

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap base	G8.5
Operating position	UNIVERSAL [Any or Universal (U)]
Flux measurement reference	Sphere
Life to 50% failures (nom.)	15,000 h

Operating and Electrical	
Arc Length O (Nom)	7.75 mm
Power Consumption	73.2 W
Voltage (nom.)	88 V

Light Technical	
Colour Code	942 [CCT of 4200K]
Luminous Flux	7,450 lm
Colour designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.371
Chromaticity Coordinate Y (Nom)	0.366
Correlated Colour Temperature (Nom)	4200 K
Luminous efficacy (rated) (nom.)	102 lm/W
Colour rendering index (CRI)	92

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T14
Net Weight (Piece)	0.009 kg

# MASTERCoulour CDM-TC Elite

## Approval and Application


Energy Efficiency Class	F
Mercury (Hg) content (max.)	6.6 mg
Mercury (Hg) content (nom.)	6.6 mg
Energy consumption kWh/1,000 hours	74 kWh
EPREL Registration Number	473275
CE mark	Yes

## Product Data

Order product name	MASTERC CDM-TC Elite 70W/942 G8.5 ICT
Full product name	MASTERC CDM-TC Elite 70W/942 G8.5 ICT


Full EOC	871829116368800
Order code	928193905131
Material no. (12 NC)	928193905131
Local order code	70CDMTCElite942
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291163688
Numerator – packs per outer box	12
EAN/UPC – Case	8718291163695

## Dimensional drawing




Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC Elite 70W/942 G8.5 ICT	15 mm	7.75 mm	51 mm	53 mm	52 mm	85 mm

## Photometric data





Spectral Power Distribution Colour - MASTERC CDM-TC Elite 70W/942 G8.5 ICT



Light Distribution Diagram - MASTERC CDM-TC Elite 70W/942 G8.5 ICT

# MASTERC colour CDM-TC Elite

## Lifetime



Lumen Maintenance Diagram - MASTERC CDM-TC Elite 70W/942 G8.5 1CT

LDLE\_CDMTC-E\_0007-Life expectancy diagram

