



MSR Platinum (Studio)

MSR Platinum 35 ST

MSR Platinum 35 ST has been specially designed for the studio/theater world, where consistent high-quality light output, high brightness and excellent color rendering are important. This lightweight, compact system delivers intense, cool-white light for the most amazing light experience. It's a powerful and innovative tool, giving lighting designers far greater freedom and delivering the same good light quality as other MSR lamps. The exceptionally short arc generates sparkling, bright light, and the lamp's ultra-compact design makes it suitable for smaller lighting fixtures. The MSR Platinum 35 ST lamp has a balanced spectrum with extra red content for enhanced color rendering.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	PGJX36
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	750 hour(s)
Light Technical	
Color Code	- [Not Specified]
Luminous Flux	54,400 lm


Correlated Color Temperature (Nom)	6000 K
Luminous Efficacy (rated) (Nom)	69.2 lm/W
Color rendering index (CRI)	75
Arc Length O (Nom)	3.8 mm
Operating and Electrical	
Power Consumption	786 W

MSR Platinum (Studio)

Lamp Current (Nom)	11.5 A
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Net Weight (Piece)	0.117 lb
Approval and Application	
CE mark	Yes
Product Data	
Order product name	MSR Platinum 35 ST


Full product name	MSR Platinum 35 ST
Full product code	871829170406500
Order code	293159
Material Nr. (12NC)	928194505114
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291704065
Numerator - Packs per outer box	16
EAN/UPC - Case	8718291704072

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR	1 inch	3/16	2-3/16	2-1/4	2-1/4	4-9/16	1-7/16
Platinum 35		inch	inch	inch	inch	inch	inch
ST							

Photometric data



Spectral Power Distribution Colour - MSR Platinum 35 ST

MSR Platinum (Studio)

